

SERVER TECHNOLOGY, INC.
PROPRIETARY INFORMATION



THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.


RoHS COMPLIANT

REVISIONS			
REV	DESCRIPTION	DATE	DFT/APPR
1	INITIAL DESIGN	11/1/11	MB/TI


NOTES:



Part Number		Input		Output				
Master	Expansion	Rating, North America	Input Type	Output Rating North America	Outlet: North America	Outlet Type	Branch Circuit: North America	Phase: North America
CW-24VDX454A1	CX-24VDX454A1	240V 3W+PE, 50/60Hz; 48A	IEC 60309	240V, 50/60Hz; <= 83.1A	6xC19 <= 16A each, 18xC13 <= 12A each	IEC 60320 C13 and C19	XY1, XY2, YZ1, YZ2, ZX1, ZX2 <= 20A	XY, YZ, ZX <= 27.7 A
CW-24VDV454A1	CX-24VDV454A1	240V 3W+PE, 50/60Hz; 40A	CS8365C	240V, 50/60Hz; <= 69.3A	6xC19 <= 16A each, 18xC13 <= 12A each	IEC 60320 C13 and C19	XY1, XY2, YZ1, YZ2, ZX1, ZX2 <= 20A	XY, YZ, ZX <= 23.1 A
CW-24VDW454A1	CX-24VDW454A1	240V 3W+PE, 50/60Hz; 48A	IEC 60309	240V, 50/60Hz; <= 83.1A	6xC19 <= 16A each, 18xC13 <= 12A each	IEC 60320 C13 and C19	XY1, XY2, YZ1, YZ2, ZX1, ZX2 <= 20A	XY, YZ, ZX <= 27.7 A
CW-24VD1454A1	CX-24VD1454A1	240V 3W+PE, 50/60Hz; 48A	None	240V, 50/60Hz; <= 83.1A	6xC19 <= 16A each, 18xC13 <= 12A each	IEC 60320 C13 and C19	XY1, XY2, YZ1, YZ2, ZX1, ZX2 <= 20A	XY, YZ, ZX <= 27.7 A
CW-24VYY454A1	CX-24VYY454A1	120/208V 3W+N+PE, 50/60Hz; 48A	IEC 60309	208V, 50/60Hz; <= 83.1A	6xC19 <= 16A each, 18xC13 <= 12A each	IEC 60320 C13 and C19	XY1, XY2, YZ1, YZ2, ZX1, ZX2 <= 20A	XY, YZ, ZX <= 27.7 A



DETAIL A
 EXPANSION UNIT

SERVER TECHNOLOGY, INC. 

1040 Sandhill Drive Reno, NV 89521

DRAWING TITLE:
**FUNCTIONAL BLOCK WIRING DIAGRAM
 SWITCHED V24**

SIZE B	CAGE CODE 049V0	DWG NO. 495-0372-3	REV 1
SCALE: 1/1		SHEET 1 OF 1	