

Sentry Basic CDU

Key Features


- > Power Distribution: 110V, 208V, 230V, 20 or 30-Amp power input feed
- > Low Density: Single-power input feed; 12 or 24 outlets per enclosure
- > Branch Circuit Protection : Sentry CDUs meet UL 60950-1 requirements
 - > Overcurrent protection with UL-listed Bussman fuses
- > Rack-Mountable : Includes horizontal and Zero U

Low-Density Basic Power Distribution

The Sentry Basic Cabinet (Power) Distribution Unit (CDU) product family provides a simple solution where reliable power distribution for equipment racks and other data center applications is needed. Basic CDU's provide both power distribution and branch circuit protection for the 30-Amp rated devices.

The Sentry Basic CDU offers different input and output connections to distribute 110V, 208V or 230V power and a 20 or 30-Amp power input feed. 30-Amp models feature a combination of white and black outlets to easily distinguish between each branch circuit.

The Sentry Basic CDU meets the criteria of Branch Circuit Protection by providing overcurrent protection with UL-listed Bussman® SC fuses for each branch circuit. Branch circuit protection is accomplished via UL-listed Bussman SC fuses for compliance with UL/CSA/EN 60950-1 standards. The Sentry "Basic" Cabinet Power Distribution Unit (CDU) family provides both a reliable and economical solution for your basic power needs.



Model	Available Input Voltages	Amperage	Available Input Cord	Outlets	Dimensions
CB-12H1-C20*	100-120V 50/60Hz	20A	IEC 60320/C20 Power Inlet	(12) NEMA 5-20R	17.0 x 1.75 x 2.25 in (432 x 44 x 57 mm)
CB-12H1-L530	100-120V 50/60Hz	30A	NEMA L5-30P Cordset, 10ft (3m)	(12) NEMA 5-20R	17.0 x 1.75 x 2.25 in (432 x 44 x 57 mm)
CB-12H2-C20*	200-240V 50/60Hz	16/20A	IEC 60320/C20 Power Inlet	(12) IEC 60320/C13	17.0 x 1.75 x 2.25 in (432 x 44 x 57 mm)
CB-12H2-L630	200-240V 50/60Hz	30A	NEMA L6-30P Cordset, 10ft (3m)	(12) IEC 60320/C13	17.0 x 1.75 x 2.25 in (432 x 44 x 57 mm)
CB-24V1-C20*	100-120V 50/60Hz	20A	IEC 60320/C20 Power Inlet	(24) NEMA 5-20R	31.25 x 1.75" x 2.25 in (794 x 44 x 57 mm)
CB-24V1-L530	100-120V 50/60Hz	30A	NEMA L5-30P Cordset, 10ft (3m)	(24) NEMA 5-20R	31.25 x 1.75" x 2.25 in (794 x 44 x 57 mm)
CB-24V2-C20*	200-240V 50/60Hz	16/20A	IEC 60320/C20 Power Inlet	(24) IEC 60320/C13	31.25 x 1.75" x 2.25 in (794 x 44 x 57 mm)
CB-24V2-L630	200-240V 50/60Hz	30A	NEMA L6-30P Cordset, 10ft (3m)	(24) IEC 60320/C13	31.25 x 1.75" x 2.25 in (794 x 44 x 57 mm)

*Power cords sold separately

Additional Specifications

Agency Approvals

- > US & Canada (cTUVus mark) to UL 60950-1:2003 and CAN/CSA 22.2 No. 60950-1-03
- > European Union (TUVGS mark) to EN 60950-1:2001
- > FCC Class A, Part 15
- > CE
- > EMC to EN 55022 Class A, EN 55024, CISPR 22 Class A

Power Cord Options

- > PTCORD-1 IEC 60320/C19 - NEMA L6-20P (20A Twist-Lock) 10'
- > PTCORD-2 IEC 60320/C19 - Schuko 10'
- > PTCORD-3 IEC 60320/C19 - IEC 60309 (BS4343, CEE17) 16/20A Blue (UK Commando) 10'
- > PTCORD-4 IEC 60320/C19 - BS1363 13A (UK) 10'
- > PTCORD-5 IEC 60320/C19 - 5-15P (15A Straight-Blade) 10'
- > PTCORD-6 IEC 60320/C19 - 5-20P (20A Straight-Blade) 10'
- > PTCORD-7 IEC 60320/C19 - L5-20P (20A Twist-Lock) 10'



Server Technology

HEADQUARTERS - NORTH AMERICA

Server Technology, Inc.
1040 Sandhill Drive
Reno, NV 89521
United States
1.775.284.2000 Tel
1.775.284.2065 Fax
sales@servertech.com
www.servertech.com
www.servertechblog.com

EMEA

Server Technology Intl
Sienna Court
The Broadway
Maidenhead
Berkshire
SL6 1NJ
United Kingdom
+44 (0) 1628 509053 Tel
+44 (0) 1628 509100 Fax
salesintl@servertech.com

APAC

Server Technology Intl
37th Floor, Singapore Land Tower
50 Raffles Place
Singapore 048623
+65 (0) 6829 7008 Tel
+65 (0) 6234 4574 Fax
salesintl@servertech.com

