

# Sentry Smart CDU

## Key Features

- > High Density: Single-power input feed; 36 outlets per enclosure (24 x C13 & 12 x C19 outlets)
- > High Power Distribution: 208 Three phase power with a 50 or 60-Amp power input feed.
- > Input Current Monitor: Precisely measure the aggregate current draw (in amps) on each branch circuit. On-site verification of the input current with the LED digital display. Remote verification via web browser or serial screen.
- > IP Access & Security: Web interface, SSL, SSH, Telnet, SNMP, FTP, SNT, Syslog, LDAP, LDAPS, RADIUS, TACACS and RS-232 access
- > Alerts: Provide automated SNMP-based alarms or email alerts for power and environmental conditions
- > Environmental Monitoring: Each Smart CDU supports two external temperature & humidity probes and reports conditions through the user interface without the need for additional IP addresses

## CS-36VD/Y Mixed Outlets

The CS-36VD/Y Smart Cabinet Distribution Unit (CDU) provides reliable power distribution for high density applications such as blade server clusters that require 3-Phase, 50-Amp or 60-Amp power. The Smart CDU provides reliable power distribution combined with local and remote power monitoring and environmental monitoring via IP. Use the network interface to view power, temperature and humidity levels via Web browser, or receive SNMP-based alarms and email alerts when conditions exceed defined thresholds.

It utilizes new Digital True RMS current monitoring with the highest accuracy and resolution available in the market today.

## Additional Benefits:



### Branch Circuit Protection

The Sentry CDU Family meets the UL 60950-1 requirement for branch circuit protection.  
- UL 489 rated circuit breakers



### Branch Current Monitoring

Exclusive Digital True RMS current monitoring is critical to preventing overloads in high-density computing environments. LED digital displays on the CDU enclosure report the input current of each branch circuit (a total of 6 LED current monitors) for load balancing



### Temperature and Humidity

The Smart CDU supports two external 10' (3m) probes. Each of these probes measure both temperature and humidity. Receive SNMP-based alerts or email notifications when conditions exceed defined thresholds.



Model	Available Input Voltages	Amperage	Available Input Cord	Outlets	Dimensions (L x W x D)
CS-36VDX813A4 CL-36VDX813A4	3-Phase Delta, 208 V 50/60Hz	60A	IEC 60309 Cordset, 10 ft (3.0 m)	(24) IEC 60320/C13 (12) IEC 60320/C19	70.0 x 3.5 x 3.5 in. (1778 x 89 x 89 mm)
CS-36VYY813A4 CL-36VYY813A4	3-Phase Wye, 208 V 50/60Hz	60A	IEC 60309 Cordset, 10 ft (3.0 m)	(24) IEC 60320/C13 (12) IEC 60320/C19	70.0 x 3.5 x 3.5 in. (1778 x 89 x 89 mm)
CS-36VDV813A4 CL-36VDV813A4	3-phase Delta, 208V 50/60Hz	50A	CS8365 Cordset, 10 ft (3.0 m)	(24) IEC 60320/C13 (12) IEC 60320/ C19	70.0 x 3.5 x 3.5 in. (1778 x 89 x 89 mm)

\*CL refers to the Expansion Module

## Additional Features and Specifications

### Agency Approvals

- > US & Canada (cULus mark) to UL 60950-1:2003 and CAN/CSA 22.2 No. 60950-1-03
- > cULus Mark to UL 60950-1:2003 and CAN/CSA 22.2 No. 60950-1:2003
- > FCC Class A, Part 15
- > CE
- > EMC to EN 55022 Class A, EN 55024, CISPR 22 Class A

### Communications and Security

- > 10/100 BaseT Ethernet
- > HTTP/HTTPS
- > SSLv3/TLSv1
- > SNMPv2
- > SSHv2
- > Telnet
- > LDAPS/LDAPv3
- > RADIUS
- > TACACS+
- > RS-232 (Serial)

### Branch Circuit Protection

- > Compliant to UL 60950-1

### Accessories

- > Optional Temperature & Humidity Probe
  - EMTH-1-1 Temperature & Humidity Probe, 10 ft (3m)
- > SPM (Sentry Power Manager) Appliance:
  - Monitor and Manage multiple Sentry CDU's
  - Monitor and Manage all alarm conditions
  - Reporting and Trending
  - Group or Cluster outlets for reboot and power information
- > Environmental Monitor
  - EMCU-1-1 allows up to (2) additional temperature & humidity probes, (1) water sensor, (4) dry contact closures, (1) analog-to-digital contact sensor. Includes (1) temperature/humidity probe with unit.



### Expansion Module Model Numbers

- > CL-36VDX813A4
- > CL-36VYY813A4
- > CL-36VDV813A4



## Server Technology

HEADQUARTERS - NORTH AMERICA  
 Server Technology, Inc.  
 1040 Sandhill Drive  
 Reno, NV 89521  
 United States  
 1.775.284.2000 Tel  
 1.775.284.2065 Fax  
 sales@servertech.com  
 www.servertech.com  
 www.servertechblog.com

EMEA  
 Server Technology Intl  
 Sienna Court  
 The Broadway  
 Maidenhead  
 Berkshire  
 SL6 1NJ  
 United Kingdom  
 +44 (0) 1628 509053 Tel  
 +44 (0) 1628 509100 Fax  
 salesintl@servertech.com

APAC  
 Server Technology Intl  
 37th Floor, Singapore Land  
 Tower  
 50 Raffles Place  
 Singapore 048623  
 +65 (0) 6829 7008 Tel  
 +65 (0) 6234 4574 Fax  
 salesintl@servertech.com