

# Sentry Smart CDU

## Key Features

- > High Density: Single-power input feed; 18 outlets per enclosure
- > High Power Distribution: 230/400 V, 3-phase Wye, 16/32 Amp power input feeds
- > Input Current Monitor: Precisely measure the aggregate current draw (in amps) on each phase. On-site verification of the input current with the LED digital display. Remote verification via web browser or serial screen.
- > IP Access & Security: Web interface, SSL, SSH, Telnet, SNMP, FTP, SNTp, Syslog, LDAP, LDAPS, RADIUS, TACACS and RS-232 access
- > SNMP Traps & Alerts: Provide automated SNMP-based alarms or Email alerts for power and environmental conditions
- > Environmental Monitoring: Each Smart CDU supports two external temperature & humidity probes and reports conditions thru the user interface without the need for additional IP addresses
- > Add an Expansion Module: Connect the Smart Expansion CDU (CL) to a Master unit (CS) for power monitoring of separate power circuits from a single IP address

## CS-18V4 with C19 Outlets

### High Density Power Distribution

The Smart Cabinet Distribution Units (CDU) provide reliable power distribution combined with local and remote power monitoring and environmental monitoring via IP. Use the network interface to view power, temperature and humidity levels via Web browser, or receive SNMP-based alarms and email alerts when conditions exceed defined thresholds.

The Smart CDU family has the capability to daisy chain units together. The Expansion CDU Module gives the ability to use one IP address across different power circuits.

### Additional Benefits:



#### Branch Circuit Protection

The Sentry CDU Family meets the UL 60950-1 requirement for branch circuit protection.

- UL 489 rated circuit breakers



#### Input Current Monitoring

Exclusive Digital True RMS current monitoring is critical to preventing overloads in high-density computing environments. LED digital display on the CDU enclosure reports the input current of each phase.



#### Temperature and Humidity

The Smart CDU supports two external 10' (3m) probes. Each of these probes measure both temperature and humidity. Receive SNMP-based alerts or email notifications when conditions exceed defined thresholds.



#### Linking for Smart CDU (Expansion Modules)

The Smart CDU family has the capability to daisy chain units together. The Expansion Module provides the ability to link two power circuits under one IP address.



Model	Available Input Voltages	Amperage	Available Input Cord**	Outlets	Dimensions (L x W x D)
CS-18V4J413A3 CL-18V4J413A3*	230/400V, 3-phase Wye, 50/60Hz	16A	IEC 60309 Cord Set 3m (10 ft)	(18) IEC 60320/C19	69.0 x 1.75 x 3.50 in. (1752 x 44 x 89 mm)
CS-18V4K413A3 CL-18V4K413A3*	230/400V, 3-phase Wye, 50/60Hz	32A	IEC 60309 Cord Set 3m (10 ft)	(18) IEC 60320/C19	69.0 x 1.75 x 3.50 in. (1752 x 44 x 89 mm)

\* CL part numbers refer to the Expansion CDU

## Additional Features and Specifications

### Agency Approvals

- > European Union (TUVGS Mark) to EN 60950-1:2001
- > FCC Class A, Part 15
- > CE
- > EMC to EN 55022 Class A, EN 55024 CISPR 22 Class A

### Communications and Security

- > 10/100 BaseT Ethernet
- > HTTP/HTTPS
- > SSLv3/TLSv1
- > SNMPv2
- > SSHv2
- > Telnet
- > LDAPS/LDAPv3
- > TACACS+
- > RADIUS
- > RS-232 (Serial)

### Branch Circuit Protection

- > Compliant to UL 60950-1

### Accessories

- > Optional Temperature & Humidity Probe
  - EMTH-1-1 Temperature & Humidity Probe, 10 ft (3m)
- > Environmental Monitor
  - EMCU-1-1B allows up to (2) additional temperature & humidity probes, (1) water sensor, (4) dry contact closures, (1) analog-to-digital contact sensor. Includes (1) temperature/humidity probe with unit.
- > SPM (Sentry Power Manager) Appliance:
  - Monitor and Manage multiple Sentry CDU's
  - Monitor and Manage all alarm conditions
  - Reporting and Trending
  - Group or Cluster outlets for reboot and power information



### Expansion Module Model Number

- > CL-18V4J413A3
- > CL-18V4K413A3



## Server Technology

HEADQUARTERS - NORTH AMERICA  
 Server Technology, Inc.  
 1040 Sandhill Drive  
 Reno, NV 89521  
 United States  
 1.775.284.2000 Tel  
 1.775.284.2065 Fax  
 sales@servertech.com  
 www.servertech.com  
 www.servertechblog.com

EMEA  
 Server Technology Intl  
 Sienna Court  
 The Broadway  
 Maidenhead  
 Berkshire  
 SL6 1NJ  
 United Kingdom  
 +44 (0) 1628 509053 Tel  
 +44 (0) 1628 509100 Fax  
 salesint@servertech.com

APAC  
 Server Technology Intl  
 37th Floor, Singapore Land Tower  
 50 Raffles Place  
 Singapore 048623  
 +65 (0) 6829 7008 Tel  
 +65 (0) 6234 4574 Fax  
 salesint@servertech.com