

Sentry Smart CDU

CS-42VD/VY 3-Phase 50/60A

High Density Power Distribution

The Smart Cabinet Distribution Units (CDU) provide reliable power distribution combined with local and remote power monitoring and environmental monitoring via IP. Use the network interface to view power, temperature and humidity levels via Web browser, or receive SNMP-based alarms and email alerts when conditions exceed defined thresholds.

The Smart CDU family has the capability to daisy chain units together. The Expansion CDU Module gives the ability to use one IP address across different power circuits.


Additional Benefits:



Branch Circuit Protection


The Sentry CDU Family meets the new UL 60950-1 requirement for branch circuit protection.

- UL 489 rated circuit breakers



Input Current Monitoring

The NEW Digital True RMS current monitoring, with improved accuracy, is critical to preventing overloads in high-density computing environments. LED digital displays on the CDU enclosure which report the input current of each input phase for simple load balancing.



Temperature and Humidity

The Smart CDU supports two external 10' (3m) probes. Each of these probes measure both temperature and humidity. Receive SNMP-based alerts or email notifications when conditions exceed defined thresholds.



Linking for Smart CDU (Expansion Modules)

The Smart CDU family has the capability to daisy chain units together. The Expansion Module provides the ability to link two power circuits under one IP address.

Key Features

- > High Density: Single-power input feed; 42 outlets per enclosure (Quantity 42 IEC 60320 C13 outlets)
- > High Power Distribution: Three phase 208-240V power options; 50 and 60 Amp power input feed
- > Input Current Monitor: Precisely measure the aggregate current draw (in amps) on each input power phase. On-site verification of the input current with the LED digital display. Remote verification via web browser or serial screen.
- > IP Access & Security: Web interface, SSL, SSH, Telnet, SNMP, FTP, SNT, Syslog, LDAP, LDAPS, RADIUS, TACACS and RS-232 access
- > SNMP Traps & Alerts: Provide automated SNMP-based alarms or Email alerts for power and environmental conditions
- > Environmental Monitoring: Each Smart CDU supports two external temperature & humidity probes and reports conditions thru the user interface without the need for additional IP addresses
- > Add an Expansion Module: Connect the Smart Expansion CDU (CL) to a Master unit (CS) for power monitoring of separate power circuits from a single IP address



Model	Available Input Voltages	Amperage	Available Input Cord	Outlets	Dimensions (L x W x D)
CS-42VDX411 CL-42VDX411*	240V, 3-phase Delta, 50/60Hz	60A	IEC Blue 9hr 3P+G Plug, 10'(3m), Bottom/Frt Cord	(42) IEC 60320/C13	76.0 x 1.75 x 3.50 in. (1930 x 44 x 89 mm)
CS-42VDV411 CL-42VDV411*	240V, 3-phase Delta, 50/60Hz	50A	CS8365C Plug, 10'(3m), Bottom/Frt Cord	(42) IEC 60320/C13	76.0 x 1.75 x 3.50 in. (1930 x 44 x 89 mm)
CS-42VYY411 CL-42VYY411*	208V, 3-phase Wye, 50/60Hz	60A	IEC Blue 9hr 3P+N+G Plug, 10'(3m), Bottom/Frt Cord	(42) IEC 60320/C13	76.0 x 1.75 x 3.50 in. (1930 x 44 x 89 mm)

* CL part numbers refer to the Expansion CDU

Additional Features and Specifications

Agency Approvals

- > US & Canada (cTUVus Mark) to UL 60950-1:2003 and CAN/CSA 22.2 No. 60950-1-03
- > FCC Class A, Part 15
- > CE
- > EMC to EN 55022 Class A, EN 55024, CISPR 22 Class A

Communications and Security

- > 10/100 BaseT Ethernet
- > HTTP/HTTPS
- > SSLv3/TLSv1
- > SNMPv2
- > SSHv2
- > Telnet
- > LDAPS/LDAPv3
- > TACACS+
- > RADIUS
- > RS-232 (Serial)

Branch Circuit Protection

- > Compliant to UL 60950-1

Accessories

- > Optional Temperature & Humidity Probe
 - EMTH-1-1 Temperature & Humidity Probe, 10 ft (3m)
- > SPM (Sentry Power Manager) Appliance:
 - Monitor and Manage multiple Sentry CDU's
 - Monitor and Manage all alarm conditions
 - Reporting and Trending
 - Group or Cluster outlets for reboot and power information
- > Environmental Monitor
 - EMCU-1-1B allows up to (2) additional temperature & humidity probes, (1) water sensor, (4) dry contact closures, (1) analog-to-digital contact sensor. Includes (1) temperature/humidity probe with unit.

1U SPM Appliance



Expansion Module

- Model Numbers
- >CL-42VDX411
 - >CL-42VDV411
 - >CL-42VYY411



Server Technology

HEADQUARTERS - NORTH AMERICA
 Server Technology, Inc.
 1040 Sandhill Drive
 Reno, NV 89521
 United States
 1.775.284.2000 Tel
 1.775.284.2065 Fax
 sales@servertech.com
 www.servertech.com
 www.servertechblog.com

EMEA
 Server Technology Intl
 Sienna Court
 The Broadway
 Maidenhead
 Berkshire
 SL6 1NJ
 United Kingdom
 +44 (0) 1628 509053 Tel
 +44 (0) 1628 509100 Fax
 salesintl@servertech.com

APAC
 Server Technology Intl
 37th Floor, Singapore Land
 Tower
 50 Raffles Place
 Singapore 048623
 +65 (0) 6829 7008 Tel
 +65 (0) 6234 4574 Fax
 salesintl@servertech.com