

Sentry Switched CDU

CW-24V5 with 12xC13 & 12xC19 Outlets, 240/415V

High-Density Power Distribution

The Switched CDU combines remote configuration and management with power distribution and power and environmental monitoring. Reboot a single or dual-power server with one command. Receive SNMP or email-based alerts when power or environmental conditions exceed thresholds. Assign user specific access rights to designated outlets or groups.

This Switched CDU has middle entry for network, serial & environmental connections combined with a bottom power cord entry. This provides the ultimate flexibility when connecting Switched CDU's to raised floors, overhead power or busways.. Current monitors are easily inverted via the web GUI or serial interface.

Additional Benefits:



Branch Circuit Protection

The Sentry CDU Family meets the UL 60950-1 requirement for Branch Circuit Protection
 > UL-489 rated circuit breakers



PIPS - Per Input Power Sensing

Accurately measures Active Power, Apparent Power, Energy k-Wh, Power Capacity, and Power Capacity Used using the network interface. See the aggregate current draw, in Amps, locally using the onboard LED.



Temperature and Humidity

The Switched CDU supports two external 10ft (3m) probes. Each of these probes measure both temperature and humidity. Receive SNMP-based alerts or email notifications when conditions exceed defined thresholds.



Mixed Outlets

This Switched CDU combines both IEC 60320/C13 and IEC 60320/C19 switched outlets within a single CDU. For rebooting non-responsive servers & network devices.

Key Features

- > **High Density:** Single-power input feed; 24 outlets per enclosure (12 IEC C13 and 12 IEC C19 outlets)
- > **High Power Distribution:** 240/415V, 3-Phase Wye, 20A or 30A power input feed options.
- > **Input Current Monitor:** Precisely measure the aggregate current draw (in amps) on each phase. On-site verification of the input current with LED digital displays. Remote verification via web browser or serial screen.
- > **Remote Power Management:** Power cycle individual power outlets, or groups of power outlets, to remotely reboot servers and network devices, anywhere in the world. Or, power-off unused power receptacles
- > **IP Access & Security:** Web interface, SSL, SSH, Telnet, SNMP, FTP, SNTp, Syslog, LDAP, LDAPS, RADIUS, TACACS and RS-232 access
- > **SNMP Traps and Email alerts:** Provide automated alerts for power and environmental conditions
- > **Environmental Monitoring:** Each Switched CDU supports two external temperature & humidity probes and reports conditions thru the user interface without the need for additional IP addresses
- > **Add an Expansion Module:** Connect the Switched Expansion CDU (CX) to a Master unit (CW) for power monitoring of separate power circuits from a single IP address



Model	Available Input Voltages	Amperage	Available Input Cord	Outlets	Dimensions (L x W x D)
CW-24V53425A9 CX-24V53425A9*	240/415V 3-Phase Wye, 50/60Hz	20A	IEC Red 6hr 3P+N+G Plug, 10'(3m), Bottom/Frt Cord	(12) IEC 60320/C13 (12) IEC 60320/C19	70.6 x 1.75 x 3.50 in. (1794 x 44 x 89 mm)
CW-24V54425A9 CX-24V54425A9*	240/415V 3-Phase Wye, 50/60Hz	30A	IEC Red 6hr 3P+N+G Plug, 10'(3m), Bottom/Frt Cord	(12) IEC 60320/C13 (12) IEC 60320/C19	70.6 x 1.75 x 3.50 in. (1794 x 44 x 89 mm)
CW-24V5Z425A9 CX-24V5Z425A9*	240/415V 3-Phase Wye, 50/60Hz	30A	NEMA L22-30P Plug, 10'(3m), Bottom/Frt Cord	(12) IEC 60320/C13 (12) IEC 60320/C19	70.6 x 1.75 x 3.50 in. (1794 x 44 x 89 mm)

* CX part numbers refer to the Expansion CDU

Additional Features and Specifications

Agency Approvals

- > US & Canada (cTUVus mark) to UL 60950-1:2003 and CAN/CSA 22.2 No. 60950-1-03
- > FCC Class A, Part 15
- > EMC to EN 55022 Class A, EN 55024, CISPR 22 Class A
- > CE

Communications and Security

- > 10/100 BaseT Ethernet
- > HTTP/HTTPS
- > SSLv3/TLSv1
- > SNMPv2
- > SSHv2
- > Telnet
- > LDAPv3
- > LDAPS
- > TACACS+
- > RADIUS
- > RS-232 (Serial)

Branch Circuit Protection

- > Compliant to UL 60950-1

Accessories

- > Optional Temperature & Humidity Probe
 - EMTH-1-1 Temperature & Humidity Probe, 10ft (3m)
- > Environmental Monitor
 - EMCU-1-1B allows up to (2) additional temperature & humidity probes, (1) water sensor, (4) dry contact closures, (1) analog-to-digital converter. Includes (1) temperature/humidity probe with unit.
- > SPM (Sentry Power Manager) Appliance:
 - Monitor and Manage multiple Sentry CDU's
 - Monitor and Manage all alarm conditions
 - Reporting and Trending
 - Group or Cluster outlets for reboot and power information

> 1U SPM Appliance



Expansion Module Model Numbers

- >CX-24V53425A9
- >CX-24V54425A9
- >CX-24V5Z425A9



Server Technology

HEADQUARTERS - NORTH AMERICA
 Server Technology, Inc.
 1040 Sandhill Drive
 Reno, NV 89521
 United States
 1.775.284.2000 Tel
 1.775.284.2065 Fax
 sales@servertech.com
 www.servertech.com
 www.servertechblog.com

EMEA
 Server Technology Intl
 Sienna Court
 The Broadway
 Maidenhead
 Berkshire
 SL6 1NJ
 United Kingdom
 +44 (0) 1628 509053 Tel
 +44 (0) 1628 509100 Fax
 salesintl@servertech.com

APAC
 Server Technology Intl
 37th Floor, Singapore Land Tower
 50 Raffles Place
 Singapore 048623
 +65 (0) 6829 7008 Tel
 +65 (0) 6234 4574 Fax
 salesintl@servertech.com