

Sentry Switched CDU

CW-48VD/VY 20/30A 3-Phase Mixed Outlet with PIPS

High-Density Power Distribution

The Switched CDU's combine remote configuration and management with power distribution and power and environmental monitoring. Reboot a single or dual-power server with one command. Receive SNMP or email based alerts when power or environmental conditions exceed thresholds. Assign users specific access rights to designated outlets or groups.

Only the Switched CDU products provide the flexibility needed for all data centers and remote sites, including power requirements for high-amp, high voltage; UL 60950-1 branch circuit protection; SSL & SSH security; and SNMP-based input current monitoring.

Additional Benefits:

Branch Circuit Protection

The Sentry CDU Family meets the new UL 60950-1 requirement for branch circuit protection.

This Sentry CDU products meet the above criteria by providing overcurrent protection with UL-listed Bussman SC fuses for each branch circuit.

PIPS - Per Input Power Sensing

Accurately measures Active Power, Apparent Power, Energy k-Wh, Power Capacity, Reactance, and Power Capacity Used using the network interface. See the aggregate current draw, in Amps, locally using the onboard LED.

Temperature and Humidity

The Switched CDU supports two external probes. Each of these probes measure both temperature and humidity. Receive SNMP-based alert notifications when conditions exceed defined thresholds.

Linking for Switched CDU (Expansion Modules)

The Switched CDU family has the capability to daisy chain units together. The Expansion Module provides the ability to link two power circuits under one IP address.

Key Features

- > Remote Power Management: Power cycle individual power outlets, or groups of power outlets, to remotely reboot servers and network devices, anywhere in the world. Or, power-off unused power receptacles
- > High Power Distribution: 208V, 3-Phase Delta or Wye, 20 or 30A power input options
- > High Density: Single power input feed; (36) IEC C13 and (12) IEC C19 outlets per enclosure
- > IP Access & Security: Web interface, SSL, SSH, Telnet, SNMP, FTP, SNT, Syslog, RADIUS, LDAP, LDAPS, TACACS and RS-232 access
- > Add an Expansion Module: Connect the Switched Expansion CDU (CX) to a Master unit (CW) for power management of separate power circuits from a single IP address
- > Environmental Monitoring: Each Switched CDU supports two temperature & humidity probes and reports conditions thru the user interface without the need for additional IP addresses
- > SNMP Traps: Provide automated alerts for power and environmental conditions
- > Input Current Monitor: Precisely measure the aggregate current draw (in amps) on each phase. On-site verification of the input current with the LED digital display. Remote verification via browser or serial screen.
- > Power-up Sequencing: Prevent an in-rush power overload



Model	Available Input Voltages	Amperage	Available Input Cord	Outlets	Dimensions (L x W x D)
CW-48VDD325A1 CX-48VDD325A1*	240V 3-Phase Delta, 50/60Hz	20A	NEMA L15-20P Plug, 10'(3m), Bottom/Frt Cord	(36) IEC 60320/C13 (12) IEC 60320/C19	69.0 x 3.50 x 3.50 in. (1753 x 89 x 89 mm)
CW-48VDE325A1 CX-48VDE325A1*	240V 3-Phase Delta, 50/60Hz	30A	NEMA L15-30P Plug, 10'(3m), Bottom/Frt Cord	(36) IEC 60320/C13 (12) IEC 60320/C19	69.0 x 3.50 x 3.50 in. (1753 x 89 x 89 mm)
CW-48VYL325A1 CX-48VYL325A1*	208V 3-Phase Wye, 50/60Hz	20A	NEMA L21-20P Plug, 10'(3m), Bottom/Frt Cord	(36) IEC 60320/C13 (12) IEC 60320/C19	69.0 x 3.50 x 3.50 in. (1753 x 89 x 89 mm)
CW-48VYM325A1 CX-48VYM325A1*	2208V 3-Phase Wye, 50/60Hz	30A	NEMA L21-30P Plug, 10'(3m), Bottom/Frt Cord	(36) IEC 60320/C13 (12) IEC 60320/C19	69.0 x 3.50 x 3.50 in. (1753 x 89 x 89 mm)

*CX part number refers to the expansion CDU

Additional Features and Specifications

Agency Approvals

- > US & Canada (cTUVus Mark) to UL 60950-1:2003 and CAN/CSA 22.2 No. 60950-1-03
- > FCC Class A, Part 15
- > CE Mark
- > EMC to EN 55022 Class A, EN 55024, CISPR 22 Class A

Communications and Security

- > 10/100 BaseT Ethernet
- > HTTP/HTTPS
- > SSLv3/TLSv1
- > SNMPv2
- > SSHv2
- > Telnet
- > RADIUS
- > LDAPv3
- > LDAPS
- > TACACS+
- > RS-232 (Serial)

Branch Circuit Protection

- > Compliant to UL 60950-1

Accessories

- > Optional Temperature & Humidity Probe
 - EMTH-1-1 Temperature & Humidity Probe, 10 ft (3m)
- > SPM (Sentry Power Manager) Appliance:
 - Monitor and Manage multiple Sentry CDU's
 - Monitor and Manage all alarm conditions
 - Reporting and Trending
 - Group or Cluster outlets for reboot and power information
- > Environmental Monitor
 - EMCU-1-1B allows up to (2) additional temperature & humidity probes, (1) water sensor, (4) dry contact closures, (1) analog-to-digital contact sensor. Includes (1) temperature/humidity probe with unit.

1U SPM Appliance



Expansion Module Model Numbers

- > CX-48VDD325A1
- > CX-48VDE325A1
- > CX-48VYL325A1
- > CX-48VYM325A1



Server Technology

HEADQUARTERS - NORTH AMERICA
 Server Technology, Inc.
 1040 Sandhill Drive
 Reno, NV 89521
 United States
 1.775.284.2000 Tel
 1.775.284.2065 Fax
 sales@servertech.com
 www.servertech.com
 www.servertechblog.com

EMEA
 Server Technology Intl
 Sienna Court
 The Broadway
 Maidenhead
 Berkshire
 SL6 1NJ
 United Kingdom
 +44 (0) 1628 509053 Tel
 +44 (0) 1628 509100 Fax
 salesint@servertech.com

APAC
 Server Technology Intl
 37th Floor, Singapore Land Tower
 50 Raffles Place
 Singapore 048623
 +65 (0) 6829 7008 Tel
 +65 (0) 6234 4574 Fax
 salesint@servertech.com