



SERVER TECHNOLOGY, INC  
 PROPRIETARY INFORMATION

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

REVISION HISTORY				
ZONE	REV	DESCRIPTION	DATE	APPROVED
-	1	INITIAL DESIGN	9/1/2010	MAR/J



Part Number		Input		Output				
Master	Expansion	Rating, North America / PSF JAPAN	Input Type	Output Rating North America / PSF JAPAN	Outlet / PSF JAPAN	Outlet Type	Branch Circuit / PSF JAPAN	Phase / PSF JAPAN
CW-30VDD458C2-012	CX-30VDD458C2-012	240 V 3W + PE, 50/60 Hz; 16 A	NEMA L15-20P	240 V, 50/60 Hz; ? 27.6 A	6x C19 ? 9.2 A each; 24x C13 ? 9.2 A each	IEC 60320 C13 and C19	XY, YZ, ZX ? 9.2 A	XY, YZ, ZX ? 9.2 A
CW-30VDE458C2-012	CX-30VDE458C2-012	240 V 3W + PE, 50/60 Hz; 24 A	NEMA L15-30P	240 V, 50/60 Hz; ? 41.6 A	6x C19 ? 13.9 A each; 24x C13 ? 12 A each	IEC 60320 C13 and C19	XY, YZ, ZX ? 13.9 A	XY, YZ, ZX ? 13.9 A
CW-30VYL458C2-012	CX-30VYL458C2-012	120/208 V 3W + N + PE, 50/60 Hz; 16 A	NEMA L21-20P	240 V, 50/60 Hz; ? 27.6 A	6x C19 ? 9.2 A each; 24x C13 ? 9.2 A each	IEC 60320 C13 and C19	XY, YZ, ZX ? 9.2 A	XY, YZ, ZX ? 9.2 A
CW-30VYM458C2-012	CX-30VYM458C2-012	120/208 V 3W + N + PE, 50/60 Hz; 24 A	NEMA L21-30P	240 V, 50/60 Hz; ? 41.6 A	6x C19 ? 13.9 A each; 24x C13 ? 12 A each	IEC 60320 C13 and C19	XY, YZ, ZX ? 13.9 A	XY, YZ, ZX ? 13.9 A

ISO VIEW

<b>TOLERANCES</b> (UNLESS OTHERWISE SPECIFIED) LINEAR DIMENSIONS: .X = ± .500 .XX = ± .300 .XXX = ± .150 ANGULAR DIMENSIONS: X = ± 1° X.X = ± .5° X.XX = ± .25° SYMBOLS (Q#) = CRITICAL DIM. (S) = COSMETIC SURFACE	UNLESS OTHERWISE SPECIFIED * INTERPRET DRAWING IAW ASME Y14.100-2000 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2007 * REMOVE ALL BURRS AND SHARP EDGES, 2/R MAX. * DIMENSIONS ARE IN MILLIMETERS * DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING. DO NOT SCALE DRAWING	THIRD ANGLE PROJECTION		<b>SERVER TECHNOLOGY, INC.</b> 1040 Sandhill Drive Reno, NV 89521 DRAWING TITLE: <b>SWITCHED PIPS CDU MODEL #CW[CX]-30Vxx 30A, 3PH, 208V, BASIC WIRING DIAGRAM</b>		
		APPROVALS	DATE		DRAWN BY: mramsey CHECKED BY: MAR/JM APPROVED BY: MAR/JM RELEASED BY: MAR/JM	
						SIZE: B CAGE CODE: 04V90 DWG NO.: 495-0536-1 SCALE: NONE FILE NO.: 495-0536-1.dwg
						SHEET: 1 OF 1