

8 7 6 5 4 3 2 1

SERVER TECHNOLOGY, INC.
PROPRIETARY INFORMATION



THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

REVISIONS			
REV	DESCRIPTION	DATE	DFT/APPR
1	INITIAL DESIGN	7/15/11	MB/TI

NOTES:



Part Number		Input		Output		Outlet		Branch Circuit		Phase
Master	Expansion	Rating	GS	Input Type	Output Rating	GS	North America	GS	North America / GS	North America / GS
CS-36V4J454-A4C	CL-36V4J454-A4C		230/400V 3W+N+PE, 50/60Hz; 16A	IEC 60309 16A		230V, 50/60Hz; <= 48A		12xC19 <= 16A each, 24xC13 <= 10A each	IEC 60320 C13 / C19 / L1a, L1b, L2a, L2b, L3a, L3b <= 16A	/ L1, L2, L3 <= 16A
CS-36V4K454-A4C	CL-36V4K454-A4C		230/400V 3W+N+PE, 50/60Hz; 32A	IEC 60309 32A		230V, 50/60Hz; <= 96A		12xC19 <= 16A each, 24xC13 <= 10A each	IEC 60320 C13 / C19 / L1a, L1b, L2a, L2b, L3a, L3b <= 16A	/ L1, L2, L3 <= 32A
CS-36V53454-A4C	CL-36V53454-A4C	240/415V 3W+N+PE, 50/60Hz; 16A		IEC 60309 16A	240V, 50/60Hz; <= 48A		12xC19 <= 16A each, 24xC13 <= 12A each	IEC 60320 C13 / C19	L1a, L1b, L2a, L2b, L3a, L3b <= 20A /	/ L1, L2, L3 <= 16A /
CS-36V54454-A4C	CL-36V54454-A4C	240/415V 3W+N+PE, 50/60Hz; 24A		IEC 60309 24A	240V, 50/60Hz; <= 72A		12xC19 <= 16A each, 24xC13 <= 12A each	IEC 60320 C13 / C19	L1a, L1b, L2a, L2b, L3a, L3b <= 20A /	/ L1, L2, L3 <= 24A /
CS-36V52454-A4C	CL-36V52454-A4C	240/415V 3W+N+PE, 50/60Hz; 24A		NEMA L22-30P	240V, 50/60Hz; <= 72A		12xC19 <= 16A each, 24xC13 <= 12A each	IEC 60320 C13 / C19	L1a, L1b, L2a, L2b, L3a, L3b <= 20A /	/ L1, L2, L3 <= 24A /

SERVER TECHNOLOGY, INC.
 1040 Sandhill Drive Reno, NV 89521

DRAWING TITLE:
FUNCTIONAL BLOCK WIRING DIAGRAM
SMART, PIPS V36

SIZE	CAGE CODE	DWG NO.	REV
B	049V0	495-0475-2	1
SCALE: 1/1		SHEET 1 OF 1	

8 7 6 5 4 3 2 1