

8 7 6 5 4 3 2 1

SERVER TECHNOLOGY, INC  
 PROPRIETARY INFORMATION

RoHS COMPLIANT





THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

REVISION HISTORY				
ZONE	REV	DESCRIPTION	DATE	APPROVED
-	A	INITIAL DESIGN	6/11/2010	MAR/

NOTES:

- DIMENSIONS ARE IN MILLIMETERS AND [ ] BRACKETS ARE IN INCHES.
- DIMENSIONS ARE NOMINAL. INFORMATION SUBJECT TO CHANGE WITHOUT NOTICE.



DETAIL A  
 SCALE 1 / 5  
 CL-27Vx (LINKED MODEL)

<b>TOLERANCES</b> (UNLESS OTHERWISE SPECIFIED): LINEAR DIMENSIONS: .X = ±.500 .XX = ±.300 .XXX = ±.130  ANGULAR DIMENSIONS: X = ± 1° X.X = ± .5° X.XX = ± .25°  <b>SYMBOLS</b> (Q #) = CRITICAL DIM. (S) = COSMETIC SURFACE	<b>UNLESS OTHERWISE SPECIFIED</b> * INTERPRET DRAWING IAW ASME Y14.100-2000 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2007 * REMOVE ALL BURRS AND SHARP EDGES .2 R MAX * DIMENSIONS ARE IN MILLIMETERS * DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING. <b>DO NOT SCALE DRAWING</b>	<b>THIRD ANGLE PROJECTION</b> 	<b>SERVER TECHNOLOGY, INC.</b> 1040 Sandhill Drive Reno, NV 89521	
	<b>MATERIAL:</b>  <b>FINISH:</b>  <b>VENDOR PART NO:</b>	<b>APPROVALS</b> DRAWN BY: mramsey CHECKED BY: MAR/TI APPROVED BY: MAR/TI RELEASED BY: MAR/TI	<b>DATE</b> 6/11/2010 6/11/2010 6/11/2010 6/11/2010	<b>DRAWING TITLE:</b> OUTLINE DRAWING, SMART, V27, (21) NEMA 5-20R, (6) L6-30R, 208V, 3PH, WYE, 30A
<b>SCALE:</b> NONE			<b>SIZE:</b> B	<b>CAGE CODE:</b> 04V90
<b>FILE NO:</b> 412-0487-1.idw			<b>DWG NO.:</b> 412-0487-1	<b>REV:</b> A
<b>SHEET:</b> 1 OF 3				

8 7 6 5 4 3 2 1

8 7 6 5 4 3 2 1

SERVER TECHNOLOGY, INC  
 PROPRIETARY INFORMATION


RoHS COMPLIANT

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.


THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

NOTES:


1. DIMENSIONS ARE IN MILLIMETERS AND [ ] BRACKETS ARE IN INCHES.
2. MOUNTING BRACKETS CAN BE MOUNTED IN SEVERAL DIFFERENT POSITIONS SEE FIG. A, B, C, AND D.
3. MAXIMUM PANEL THICKNESS FOR BUTTON INTO KEYHOLE PANEL IS 2.3MM.




\* SEE DETAIL A  
 ALLOW 3/4" CLEARANCE AT TOP OF ENCLOSURE TO ALLOW BUTTON TO MOUNT IN KEYHOLE




2 FIG. A  
 MB-0005-IPT7




2 FIG. C  
 MB-0005-IPT7



2 FIG. B  
 MB-0005-IPT7



2 FIG. D  
 MB-0005-IPT7



DETAIL A\*

TOLERANCES (UNLESS OTHERWISE SPECIFIED): LINEAR DIMENSIONS: .X = ±.500 .XX = ±.300 .XXX = ±.130  ANGULAR DIMENSIONS: X = ± 1° X.X = ± .5° X.XX = ± .25°  SYMBOLS (Q #) = CRITICAL DIM. (S) = COSMETIC SURFACE	UNLESS OTHERWISE SPECIFIED * INTERPRET DRAWING IAW ASME Y14.100-2000 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2007 * REMOVE ALL BURRS AND SHARP EDGES .2 R MAX * DIMENSIONS ARE IN MILLIMETERS * DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING. DO NOT SCALE DRAWING	THIRD ANGLE PROJECTION 	
	MATERIAL:  FINISH:  VENDOR PART NO:	APPROVALS DRAWN BY: mramsey CHECKED BY: MAR/TI APPROVED BY: MAR/TI RELEASED BY: MAR/TI	DATE 6/11/2010 6/11/2010 6/11/2010 6/11/2010

8 7 6 5 4 3 2 1

8 7 6 5 4 3 2 1

SERVER TECHNOLOGY, INC  
 PROPRIETARY INFORMATION



RoHS COMPLIANT

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

NOTES:

1. DIMENSIONS ARE IN MILLIMETERS AND [ ] BRACKETS ARE IN INCHES.
2. HIDDEN BRACKETS SHOWN ARE DIFFERENT OPTIONS FOR MOUNTING.
3. DIMENSIONS ARE NOMINAL. INFORMATION SUBJECT TO CHANGE WITHOUT NOTICE.



<p><b>TOLERANCES</b>          (UNLESS OTHERWISE SPECIFIED):          LINEAR DIMENSIONS:          .X = ±.500          .XX = ±.300          .XXX = ±.130</p> <p>ANGULAR DIMENSIONS:          X = ± 1°          X.X = ± .5°          X.XX = ± .25°</p> <p>SYMBOLS          (Q #) = CRITICAL DIM.          (S) = COSMETIC SURFACE</p>	<p>UNLESS OTHERWISE SPECIFIED          * INTERPRET DRAWING IAW ASME Y14.100-2000          * DIMENSIONING &amp; TOLERANCING IAW ASME Y14.5M-2007          * REMOVE ALL BURRS AND SHARP EDGES .2 R MAX          * DIMENSIONS ARE IN MILLIMETERS          * DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING.          DO NOT SCALE DRAWING</p>	<p>THIRD ANGLE PROJECTION</p>		<p><b>SERVER TECHNOLOGY, INC.</b>          1040 Sandhill Drive Reno, NV 89521</p>			
	<p>MATERIAL:</p>	<p>APPROVALS</p> <p>DRAWN BY: mramsey</p>	<p>DATE</p> <p>6/11/2010</p>	<p>DRAWING TITLE:  <b>OUTLINE DRAWING, SMART, V27, (21)</b>  <b>NEMA 5-20R, (6) L6-30R, 208V, 3PH,</b>  <b>WYE, 30A</b></p>			
	<p>FINISH:</p>	<p>CHECKED BY: MAR/TI</p>	<p>6/11/2010</p>	<p>SIZE</p> <p>B</p>	<p>CAGE CODE</p> <p>04V90</p>	<p>DWG NO.</p> <p>412-0487-1</p>	<p>REV</p> <p>A</p>
	<p>VENDOR PART NO:</p>	<p>APPROVED BY: MAR/TI</p> <p>RELEASED BY: MAR/TI</p>	<p>6/11/2010</p> <p>6/11/2010</p>	<p>SCALE: NONE</p>	<p>FILE NO: 412-0487-1.idw</p>	<p>SHEET 3 OF 3</p>	

8 7 6 5 4 3 2 1