

SERVER TECHNOLOGY, INC
 PROPRIETARY INFORMATION



THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

| REVISION HISTORY | | | | |
|------------------|-----|----------------|-----------|----------|
| ZONE | REV | DESCRIPTION | DATE | APPROVED |
| - | 1 | INITIAL DESIGN | 4/15/2010 | MAR/ |

- NOTES:
- DIMENSIONS ARE IN MILLIMETERS AND [] BRACKETS ARE IN INCHES.
 - DIMENSIONS ARE NOMINAL. INFORMATION SUBJECT TO CHANGE WITHOUT NOTICE.
 - MOUNTING BRACKETS CAN BE MOUNTED IN SEVERAL DIFFERENT POSITIONS, SEE FIG. A, B, C, AND D.
 - MAXIMUM PANEL THICKNESS FOR BUTTON INTO KEYHOLE PANEL IS 2.3mm.
 - HIDDEN BRACKETS SHOWN ARE DIFFERENT OPTIONS FOR MOUNTING.



| | | | | |
|---|--|---|---|---|
| TOLERANCES (UNLESS OTHERWISE SPECIFIED) LINEAR DIMENSIONS: .X = ± .500 .XX = ± .300 .XXX = ± .150 ANGULAR DIMENSIONS: X = ± 1° X.X = ± .5° X.XX = ± .25° SYMBOLS (Q#) = CRITICAL DIM. (S) = COSMETIC SURFACE | UNLESS OTHERWISE SPECIFIED * INTERPRET DRAWING IAW ASME Y14.100-2000 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2007 * REMOVE ALL BURRS AND SHARP EDGES, 2/R MAX. * DIMENSIONS ARE IN MILLIMETERS * DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING. DO NOT SCALE DRAWING | THIRD ANGLE PROJECTION | | SERVER TECHNOLOGY, INC 1040 Sandhill Drive Reno, NV 89521 DRAWING TITLE: OUTLINE DRAWING, SMART PoPs/PIPS V24, (18) C13, (6) C19, OUTLETS BOTTOM/FRONT ENTRY |
| | | MATERIAL: FINISH: VENDOR PART NO: | APPROVALS DRAWN BY: mramsey CHECKED BY: TI APPROVED BY: TI RELEASED BY: | |

| | | | |
|------|-----------|-------------|-----|
| SIZE | CAGE CODE | DWG NO. | REV |
| B | 04V90 | 412-0436-11 | 1 |