



SERVER TECHNOLOGY, INC  
 PROPRIETARY INFORMATION

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.


THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

REVISION HISTORY				
ZONE	REV	DESCRIPTION	DATE	APPROVED
-	1	INITIAL DESIGN	9/1/2010	MAR/



Part Number	Expansion	Input	Output
Master	Expansion	Rating, North America	Input Type Output Rating North America Outlet: North America Outlet Type Branch Circuit: North America Phase: North America
CW-24VDX451A9	CX-24VDX451A9	240V 3W+PE, 50/60Hz; 48A	IEC 60309 240V, 50/60Hz; <= 83.1A 12x C19 <= 16A each, 12x C13 <= 12A each IEC 60320 C13 and C19 XY1, XY2, YZ1, YZ2, ZX1, ZX2 <= 20A XY, YZ, ZX <= 27.7A
CW-24VDM451A9	CX-24VDM451A9	240V 3W+PE, 50/60Hz; 40A	CS8365C 240V, 50/60Hz; <= 69.3A 12x C19 <= 16A each, 12x C13 <= 12A each IEC 60320 C13 and C19 XY1, XY2, YZ1, YZ2, ZX1, ZX2 <= 20A XY, YZ, ZX <= 23.1A
CW-24VY451A9	CX-24VY451A9	120/208V 3W+N+PE, 50/60Hz; 48A	IEC 60309 208V, 50/60Hz; <= 83.1A 12x C19 <= 16A each, 12x C13 <= 12A each IEC 60320 C13 and C19 XY1, XY2, YZ1, YZ2, ZX1, ZX2 <= 20A XY, YZ, ZX <= 27.7A



ISO VIEW

<b>TOLERANCES</b> (UNLESS OTHERWISE SPECIFIED) LINEAR DIMENSIONS: .X = ± .500 .XX = ± .300 .XXX = ± .150 ANGULAR DIMENSIONS: X = ± 1° X.X = ± .5° X.XX = ± .25° SYMBOLS (Q#) = CRITICAL DIM. (S) = COSMETIC SURFACE	UNLESS OTHERWISE SPECIFIED * INTERPRET DRAWING IAW ASME Y14.100-2000 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2007 * REMOVE ALL BURRS AND SHARP EDGES, 2/R MAX. * DIMENSIONS ARE IN MILLIMETERS * DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING. DO NOT SCALE DRAWING	THIRD ANGLE PROJECTION 		<b>SERVER TECHNOLOGY, INC.</b> 1040 Sandhill Drive Reno, NV 89521 	
		MATERIAL:  FINISH:  VENDOR PART NO:	<b>APPROVALS</b> DRAWN BY: mramsey CHECKED BY: MAR/JM APPROVED BY: MAR/JM RELEASED BY: MAR/JM	<b>DATE</b> 9/1/2010 12/10/2010 12/10/2010 12/10/2010	<b>DRAWING TITLE:</b> SWITCHED CDU MODEL #CW[CX]-24VDx A 60A, 3PH, 208V, BASIC WIRING DIAGRAM
		SIZE B	CAGE CODE 04V90	DWG NO. 495-0547-1	REV 1
		SCALE NONE	FILE NO. 495-0547-1.idw	SHEET 1	OF 1