

8

7

6

5

4

3

2

1

SERVER TECHNOLOGY, INC
PROPRIETARY INFORMATION


RoHS COMPLIANT

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	DFT/APPR
1	INITIAL DESIGN	07/25/2011	MBVB

NOTES:



Part Number		Input		Output		Output: North America		Output Type		Branch Circuit: North America / GS
Master	Expansion	Rating, North America	GS	Input Type	Output Rating North America	GS	GS	GS	GS	GS
CS-24V2A455C1	CL-24V2A455C1	208-240V, 50/60Hz; 16A		IEC 60320 C20 Inlet	208-240V, 50/60Hz; <= 16A		6xC19 <= 16A each, 18xC13 <= 12A each		IEC 60320 C13 / C19	<= 16A /
CS-24V2C455C1	CL-24V2C455C1	208-240V, 50/60Hz; 24A		NEMA L6-30P	208-240V, 50/60Hz; <= 24A		6xC19 <= 16A each, 18xC13 <= 12A each		IEC 60320 C13 / C19	<= 16A /
CS-24V2A458C1	CL-24V2A458C1	208-240V, 50/60Hz; 16A		IEC 60320 C20 Inlet	208-240V, 50/60Hz; <= 16A		6xC19 <= 16A each, 18xC13 <= 12A each		IEC 60320 C13 / C19	<= 16A /
CS-24V2C458C1	CL-24V2C458C1	208-240V, 50/60Hz; 24A		NEMA L6-30P	208-240V, 50/60Hz; <= 24A		6xC19 <= 16A each, 18xC13 <= 12A each		IEC 60320 C13 / C19	<= 16A /
CS-24VEA455C1	CL-24VEA455C1		230V, 50/60Hz; 16A	IEC 60320 C20 Inlet		230V, 50/60Hz; <= 16A	6xC19 <= 16A each, 18xC13 <= 10A each		IEC 60320 C13 / C19	/ <= 16A
CS-24VEK455C1	CL-24VEK455C1		230V, 50/60Hz; 32A	IEC 60309 32A		230V, 50/60Hz; <= 32A	6xC19 <= 16A each, 18xC13 <= 10A each		IEC 60320 C13 / C19	/ <= 16A
CS-24VEA458C1	CL-24VEA458C1		230V, 50/60Hz; 16A	IEC 60320 C20 Inlet		230V, 50/60Hz; <= 16A	6xC19 <= 16A each, 18xC13 <= 10A each		IEC 60320 C13 / C19	/ <= 16A
CS-24VEK458C1	CL-24VEK458C1		230V, 50/60Hz; 32A	IEC 60309 32A		230V, 50/60Hz; <= 32A	6xC19 <= 16A each, 18xC13 <= 10A each		IEC 60320 C13 / C19	/ <= 16A

SERVER TECHNOLOGY, INC.
1040 Sandhill Drive Reno, NV 89521

DRAWING TITLE:
FUNCTIONAL BLOCK WIRING DIAGRAM
SMART, PIPS, V24

SIZE	CAGE CODE	DWG NO.	REV
B	049V0	495-0350-24	1
SCALE:	1/1		SHEET 1 OF 1

8

7

6

5

4

3

2

1