



SERVER TECHNOLOGY, INC
 PROPRIETARY INFORMATION

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

REVISION HISTORY				
ZONE	REV	DESCRIPTION	DATE	APPROVED
-	1	INITIAL DESIGN	10/14/2010	MAR/



ISO VIEW

Part Number	Description	Rating: North America	GS	PSE Japan	Input Type	Output Rating: North America	GS	PSE Japan	Output: North America	GS	PSE	Output Type	Branch Circuit: North America / GS / PSE
CSG-24V2AK15SA1	CLG-24V2AK15SA1	200-240V, 50/60Hz, 1.6A		200-240V, 50/60Hz, 20A	ET: 60320 C20 Inlet	200-240V, 50/60Hz, $\le 1.6A$		200-240V, 50/60Hz, $\le 20A$	6cC19 $\le 1.6A$each, 18cC13 $\le 1.2A$each		6cC19 $\le 1.7A$each, 18cC13 $\le 1.5A$each	ET: 60320 C13 / C19	$\le 1.6A$ / $\le 20A$
CSG-24V2CK15SA1	CLG-24V2CK15SA1	200-240V, 50/60Hz, 2.0A		200-240V, 50/60Hz, 30A	NEB9-1E-30P	200-240V, 50/60Hz, $\le 2.0A$		200-240V, 50/60Hz, $\le 30A$	6cC19 $\le 1.6A$each, 18cC13 $\le 1.2A$each		6cC19 $\le 1.7A$each, 18cC13 $\le 1.5A$each	ET: 60320 C13 / C19	$\le 1.6A$ / $\le 20A$
CSG-24V6AK15SA1	CLG-24V6AK15SA1	230V, 50/60Hz, 1.6A			ET: 60320 C20 Inlet	230V, 50/60Hz, $\le 1.6A$			6cC19 $\le 1.6A$each, 18cC13 $\le 1.0A$each		6cC19 $\le 1.6A$each, 18cC13 $\le 1.0A$each	ET: 60320 C13 / C19	/ $\le 1.6A$ /
CSG-24V6CK15SA1	CLG-24V6CK15SA1	230V, 50/60Hz, 3.2A			ET: 60320 32A	230V, 50/60Hz, $\le 3.2A$			6cC19 $\le 1.6A$each, 18cC13 $\le 1.0A$each		6cC19 $\le 1.6A$each, 18cC13 $\le 1.0A$each	ET: 60320 C13 / C19	/ $\le 1.6A$ /

TOLERANCES
 (UNLESS OTHERWISE SPECIFIED)
 LINEAR DIMENSIONS:
 .X = ± .500
 .XX = ± .300
 .XXX = ± .150

ANGULAR DIMENSIONS:
 X = ± 1°
 X.X = ± .5°
 X.XX = ± .25°

SYMBOLS
 (Q#) = CRITICAL DIM.
 (S) = COSMETIC SURFACE

UNLESS OTHERWISE SPECIFIED
 * INTERPRET DRAWING IAW ASME Y14.100-2000
 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2007
 * REMOVE ALL BURRS AND SHARP EDGES. 2/R MAX.
 * DIMENSIONS ARE IN MILLIMETERS
 * DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING.
 DO NOT SCALE DRAWING

THIRD ANGLE PROJECTION

APPROVALS

DRAWN BY: mramsey	DATE 10/14/2010
CHECKED BY: MAR/JM	DATE 10/20/2010
APPROVED BY: MAR/JM	DATE 10/20/2010
RELEASED BY: MAR/JM	DATE 10/20/2010

MATERIAL:
 FINISH:
 VENDOR PART NO:

SERVER TECHNOLOGY, INC.
 1040 Sandhill Drive Reno, NV 89521

DRAWING TITLE:
**SMART POPS CDU MODEL
 #CS[L]G-24VEK415A1, 1PH, 230V,
 BASIC WIRING DIAGRAM**

SIZE B	CAGE CODE 04V90	DWG NO. 495-0436-18	REV 1
SCALE NONE	FILE NO. 495-0436-18.idw	SHEET 1	OF 1