

SERVER TECHNOLOGY, INC  
 PROPRIETARY INFORMATION

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.





THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

REVISION HISTORY				
ZONE	REV	DESCRIPTION	DATE	APPROVED
-	1	INITIAL DESIGN	5/2/2011	MB

NOTES:

- DIMENSIONS ARE IN MILLIMETERS AND [ ] ARE IN INCHES.
- DIMENSIONS ARE NOMINAL. INFORMATION SUBJECT TO CHANGE WITHOUT NOTICE.



<b>TOLERANCES</b> (UNLESS OTHERWISE SPECIFIED) LINEAR DIMENSIONS: .X = ± .500 .XX = ± .300 .XXX = ± .130 ANGULAR DIMENSIONS: X = ± 1° X.X = ± .5° X.XX = ± .25° SYMBOLS (Q#) = CRITICAL DIM. (S) = COSMETIC SURFACE	UNLESS OTHERWISE SPECIFIED * INTERPRET DRAWING IAW ASME Y14.100-2000 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2007 * REMOVE ALL BURRS AND SHARP EDGES .2 R MAX * DIMENSIONS ARE IN MILLIMETERS * DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING. DO NOT SCALE DRAWING	THIRD ANGLE PROJECTION 	
	MATERIAL:	APPROVALS	DATE
	FINISH:	DRAWN BY: MB	3/2/2011
	VENDOR PART NO:	CHECKED BY:	
		APPROVED BY:	
		RELEASED BY:	

**SERVER TECHNOLOGY, INC.**  
 1040 Sandhill Drive Reno, NV 89521

DRAWING TITLE:  
**OUTLINE DWG, SMART PIPS V36 (24)C13A  
 (12)C19 400V 3PH WYE, 6BR, 32A, CNTR  
 DISPLAY, TOP/TOP FRONT ENTRY**

SIZE <b>B</b>	CAGE CODE <b>04V90</b>	DWG NO. <b>412-0475-2</b>	REV <b>1</b>
SCALE: NONE		FILE NO: 412-0475-2.idw	SHEET 1 OF 3

RoHS COMPLIANT


REVISION HISTORY				
ZONE	REV	DESCRIPTION	DATE	APPROVED
-	1	INITIAL DESIGN	5/2/2011	MB

SERVER TECHNOLOGY, INC  
 PROPRIETARY INFORMATION

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

- NOTES:
- DIMENSIONS ARE IN MILLIMETERS AND [ ] ARE IN INCHES.
  - DIMENSIONS ARE NOMINAL. INFORMATION SUBJECT TO CHANGE WITHOUT NOTICE.
  - MOUNTING BRACKETS CAN BE MOUNTED IN SEVERAL DIFFERENT POSITIONS.
  - MAXIMUM PANEL THICKNESS FOR BUTTON INTO KEYHOLE PANEL IS 2.3mm.



\*SEE DETAIL A  
 ALLOW 3/4" CLEARANCE AT TOP OF ENCLOSURE TO ALLOW BUTTON TO MOUNT IN KEYHOLE




FIG. A  
 MB-0005-IPT7 [3]




FIG. B  
 MB-0005-IPT7 [3]




FIG. C  
 MB-0005-IPT7 [3]





FIG. D  
 MB-0005-IPT7 [3]



<b>TOLERANCES</b> (UNLESS OTHERWISE SPECIFIED) LINEAR DIMENSIONS: .X = ± .500 .XX = ± .300 .XXX = ± .130 ANGULAR DIMENSIONS: X = ± 1° X.X = ± .5° X.XX = ± .25° SYMBOLS (Q#) = CRITICAL DIM. (S) = COSMETIC SURFACE	UNLESS OTHERWISE SPECIFIED * INTERPRET DRAWING IAW ASME Y14.100-2000 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2007 * REMOVE ALL BURRS AND SHARP EDGES .2 R MAX * DIMENSIONS ARE IN MILLIMETERS * DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING. <b>DO NOT SCALE DRAWING</b>	THIRD ANGLE PROJECTION 	
	MATERIAL:	APPROVALS	DATE
	FINISH:	MB	3/2/2011
	VENDOR PART NO:	CHECKED BY:	
	APPROVED BY:		
	RELEASED BY:		

**SERVER TECHNOLOGY, INC.**  
 1040 Sandhill Drive Reno, NV 89521

DRAWING TITLE:  
**OUTLINE DWG, SMART PIPS V36 (24)C13A  
 (12)C19 400V 3PH WYE, 6BR, 32A, CNTR  
 DISPLAY, TOP/TOP FRONT ENTRY**

SIZE	CAGE CODE	DWG NO.	REV
B	04V90	412-0475-2	1
SCALE: NONE	FILE NO: 412-0475-2.idw	SHEET	2 OF 3

SERVER TECHNOLOGY, INC  
 PROPRIETARY INFORMATION

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.



THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

REVISION HISTORY				
ZONE	REV	DESCRIPTION	DATE	APPROVED
-	1	INITIAL DESIGN	5/2/2011	MB

NOTES:

- DIMENSIONS ARE IN MILLIMETERS AND [ ] ARE IN INCHES.
- DIMENSIONS ARE NOMINAL. INFORMATION SUBJECT TO CHANGE WITHOUT NOTICE.
- HIDDEN BRACKETS SHOWN ARE DIFFERENT OPTIONS FOR MOUNTING.
- MAXIMUM PANEL THICKNESS FOR BUTTON INTO KEYHOLE PANEL IS 2.3mm.



<b>TOLERANCES</b> (UNLESS OTHERWISE SPECIFIED) LINEAR DIMENSIONS: .X = ± .500 .XX = ± .300 .XXX = ± .130 ANGULAR DIMENSIONS: X = ± 1° X.X = ± .5° X.XX = ± .25° SYMBOLS (Q#) = CRITICAL DIM. (S) = COSMETIC SURFACE	UNLESS OTHERWISE SPECIFIED * INTERPRET DRAWING IAW ASME Y14.100-2000 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2007 * REMOVE ALL BURRS AND SHARP EDGES .2 R MAX * DIMENSIONS ARE IN MILLIMETERS * DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING. DO NOT SCALE DRAWING	THIRD ANGLE PROJECTION 		
	MATERIAL:	APPROVALS MB	DATE 3/2/2011	
	FINISH:	CHECKED BY:	APPROVED BY:	RELEASED BY:
	VENDOR PART NO:			

**SERVER TECHNOLOGY, INC.**  
 1040 Sandhill Drive Reno, NV 89521

DRAWING TITLE:  
**OUTLINE DWG, SMART PIPS V36 (24)C13A  
 (12)C19 400V 3PH WYE, 6BR, 32A, CNTR  
 DISPLAY, TOP/TOP FRONT ENTRY**

SIZE <b>B</b>	CAGE CODE <b>04V90</b>	DWG NO. <b>412-0475-2</b>	REV <b>1</b>
SCALE: NONE		FILE NO: 412-0475-2.idw	SHEET 3 OF 3