



SERVER TECHNOLOGY, INC
 PROPRIETARY INFORMATION

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

REVISION HISTORY				
ZONE	REV	DESCRIPTION	DATE	APPROVED
-	1	INITIAL DESIGN	12/16/2010	MAR/



ISO VIEW

Part Number	Expansion	Input	Input Type	Output	Outlet: North America	Outlet Type	Branch Circuit: North America	Phase: North America
CW-24VDD415A1	CX-24VDD415A1	240 V 3W + PE, 50/60 Hz, 16 A	NEMA115-20P	240 V, 50/60 Hz \leq 27.7 A	6xC19 \leq 16A each, 18xC13 \leq 12A each	IEC 60320 C13 / C19	XY, YZ, ZX \leq 9.2 A	XY, YZ, ZX \leq 9.2 A
CW-24VDE415A1	CX-24VDE415A1	240 V 3W + PE, 50/60 Hz, 24 A	NEMA115-30P	240 V, 50/60 Hz \leq 41.6 A	6xC19 \leq 16A each, 18xC13 \leq 12A each	IEC 60320 C13 / C19	XY, YZ, ZX \leq 13.9 A	XY, YZ, ZX \leq 13.9 A
CW-24VVL415A1	CX-24VVL415A1	120/208 V 3W + N + PE, 50/60 Hz, 16 A	NEMA121-20P	208V, 50/60Hz \leq 27.7 A	6xC19 \leq 16A each, 18xC13 \leq 12A each	IEC 60320 C13 / C19	XY, YZ, ZX \leq 9.2 A	XY, YZ, ZX \leq 9.2 A
CW-24VVM415A1	CX-24VVM415A1	120/208 V 3W + N + PE, 50/60 Hz, 24 A	NEMA121-30P	208V, 50/60Hz \leq 41.6 A	6xC19 \leq 16A each, 18xC13 \leq 12A each	IEC 60320 C13 / C19	XY, YZ, ZX \leq 13.9 A	XY, YZ, ZX \leq 13.9 A

TOLERANCES (UNLESS OTHERWISE SPECIFIED) LINEAR DIMENSIONS: .X = \pm .500 .XX = \pm .300 .XXX = \pm .150 ANGULAR DIMENSIONS: X = \pm 1° X.X = \pm .5° X.XX = \pm .25° SYMBOLS (C) = CRITICAL DIM. (S) = COSMETIC SURFACE	UNLESS OTHERWISE SPECIFIED * INTERPRET DRAWING IAW ASME Y14.100-2000 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2007 * REMOVE ALL BURRS AND SHARP EDGES, 2/R MAX. * DIMENSIONS ARE IN MILLIMETERS * DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING. DO NOT SCALE DRAWING	THIRD ANGLE PROJECTION 		SERVER TECHNOLOGY, INC. 1040 Sandhill Drive Reno, NV 89521 DRAWING TITLE: SWITCHED CDU MODEL #CW/CX-24VD, 208/240V WIRING DIAGRAM	
		MATERIAL: FINISH: VENDOR PART NO:	APPROVALS DRAWN BY: mramsey CHECKED BY: MAR/JM APPROVED BY: MAR/JM RELEASED BY: MAR/JM		DATE 12/16/2010 12/21/2010 12/21/2010 12/21/2010