

SERVER TECHNOLOGY, INC.
PROPRIETARY INFORMATION




THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

| REV | | DESCRIPTION | DATE | DFT/APPR |
|-----|--|----------------|------------|----------|
| 1 | | INITIAL DESIGN | 08/04/2010 | MAR/ |

NOTES:



| Part Number | Input | | Output | | | |
|--------------|-----------------------------------|-------------|---|--------------------|-------------|----------------------------|
| Model | Rating, North America / PSE Japan | Input Type | Output Rating North America / PSE Japan | Outlet / PSE Japan | Outlet Type | Branch Circuit / PSE Japan |
| CB-12H1-L530 | 100-120 V, 50/60 Hz; 24 A / 30 A | NEMA L5-30R | 100-120V, 50/60Hz; ≤24 A / ≤30 A | 16 A / ≤20 A | NEMA 5-20R | 16 A / ≤20 A |

| | | | | | |
|---|--|---|---------------------------|---|------------------|
| TOLERANCES (UNLESS OTHERWISE SPECIFIED) LINEAR DIMENSIONS: .X = ± .500 .XX = ± .300 .XXX = ± .130 ANGULAR DIMENSIONS: X.X = ± .5° X.XX = ± .25° SYMBOLS (Q#) = CRITICAL DIM. (S) = COSMETIC SURFACE | UNLESS OTHERWISE SPECIFIED * INTERPRET DRAWING IAW ASME Y14.100-2000 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-1994 * REMOVE ALL BURRS AND SHARP EDGES .2 R MAX * DIMENSIONS ARE IN MILLIMETERS * TOLERANCES ARE: DECIMALS ±3 ANGLES ±1.0° DO NOT SCALE DRAWING | THIRD ANGLE PROJECTION | | SERVER TECHNOLOGY, INC. 1040 Sandhill Drive Reno, NV 89521 DRAWING TITLE: BASIC CDU MODEL #CB-12H1-L530 24/30A, 120V BASIC WIRING DIAGRAM | |
| | | APPROVALS DRAWN BY: MRAMSEY CHECKED BY: APPROVED BY: RELEASED BY: | DATE 08/04/2010 | | SIZE D |
| SCALE: 1/1 | | FILE NO: 495-0370-2.dwg | | SHEET 1 OF 1 | |