



SERVER TECHNOLOGY, INC.  
**PROPRIETARY INFORMATION**  
 THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.  
 THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.


RoHS COMPLIANT

REVISIONS			
REV	DESCRIPTION	DATE	DFT/APPR
1	INITIAL DESIGN	07/13/11	MB/TI

NOTES:



Part Number	Expansion	Input		Output				
Master	Expansion	Rating, North America	Input Type	Output Rating North America	Outlet: North America	Outlet Type	Branch Circuit: North America	Phase: North America
CS-36VDX813A4	CL-36VDX813A4	240V 3W+PE, 50/60Hz; 48A	IEC 60309	240V, 50/60Hz; <= 83.1A	12xC19 <= 16A each, 24xC13 <= 12A each	IEC 60320 C13 and C19	XY1, XY2, YZ1, YZ2, ZX1, ZX2 <= 20A	XY, YZ, ZX <= 27.7A
CS-36VDV813A4	CL-36VDV813A4	240V 3W+PE, 50/60Hz; 40A	CS8365C	240V, 50/60Hz; <= 69.3A	12xC19 <= 16A each, 24xC13 <= 12A each	IEC 60320 C13 and C19	XY1, XY2, YZ1, YZ2, ZX1, ZX2 <= 20A	XY, YZ, ZX <= 23.1A
CS-36VYY813A4	CL-36VYY813A4	120/208V 3W+N+PE, 50/60Hz; 48A	IEC 60309	208V, 50/60Hz; <= 83.1A	12xC19 <= 16A each, 24xC13 <= 12A each	IEC 60320 C13 and C19	XY1, XY2, YZ1, YZ2, ZX1, ZX2 <= 20A	XY, YZ, ZX <= 27.7A

SERVER TECHNOLOGY, INC.   
 1040 Sandhill Drive Reno, NV 89521

DRAWING TITLE:  
**FUNCTIONAL BLOCK WIRING DIAGRAM**  
 DRAWING, SMART V36

SIZE	CAGE CODE	DWG NO.	REV
B	049V0	495-0348-1	1
SCALE: 1/1	SHEET 1 OF 1		