



SERVER TECHNOLOGY, INC.  
**PROPRIETARY INFORMATION**  
 THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.  
 THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

REVISIONS			
REV	DESCRIPTION	DATE	DFT/APPR
1	INITIAL DESIGN	07/20/2011	MB/VB

NOTES:



Part Number	Expansion	Input		Output				
		Rating, North America	Input Type	Output Rating North America	Outlet: North America	Outlet Type	Branch Circuit: North America	Phase: North America
CS-42VDV411	CL-42VDV411	240V 3W+PE, 50/60Hz; 40A	CS8365	240V, 50/60Hz; <= 69.3A	42xC13 <= 12A each	IEC 60320 C13	XY1, XY2, YZ1, YZ2, ZX1, ZX2 <= 20A	XY, YZ, ZX <= 23.1A
CS-42VDW411	CL-42VDW411	240V 3W+PE, 50/60Hz; 48A	NEMA 15-60P	240V, 50/60Hz; <= 83.1A	42xC13 <= 12A each	IEC 60320 C13	XY1, XY2, YZ1, YZ2, ZX1, ZX2 <= 20A	XY, YZ, ZX <= 27.7A
CS-42VDX411	CL-42VDX411	240V 3W+PE, 50/60Hz; 48A	IEC 60309	240V, 50/60Hz; <= 83.1A	42xC13 <= 12A each	IEC 60320 C13	XY1, XY2, YZ1, YZ2, ZX1, ZX2 <= 20A	XY, YZ, ZX <= 27.7A
CS-42VYV411	CL-42VYV411	120/208V 3W+N+PE, 50/60Hz; 48A	IEC 60309	208V, 50/60Hz; <= 83.1A	42xC13 <= 12A each	IEC 60320 C13	XY1, XY2, YZ1, YZ2, ZX1, ZX2 <= 20A	XY, YZ, ZX <= 27.7A

VHUYHUN#HFQRCR J \#0F

1040 Sandhill Drive Reno, NV 89521

DRAWING TITLE:  
**FUNCTIONAL BLOCK WIRING DIAGRAM,  
 SMART V42**

SIZE	CAGE CODE	DWG NO.	REV
B	049V0	495-0477-10	1
SCALE:	1/1	SHEET	1 OF 1