

SERVER TECHNOLOGY, INC.  
**PROPRIETARY INFORMATION**




THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

REV		DESCRIPTION	DATE	DFT/APPR
1		INITIAL DESIGN	08/04/2010	MAR/

NOTES:



Part Number	Input		Input Type	Output		Outlet: North America / PSE	Outlet Type	Branch Circuit: North America / PSE
	Rating, North America	PSE Japan		Output Rating North America	PSE Japan			
CB-12H2-L630	208-240V, 50/60Hz; 24A	200-240V, 50/60Hz; 30A	NEMA L6-30P	208-240V, 50/60Hz; ≤24A	200-240V, 50/60Hz; ≤30A	≤12A/≤15A	IEC 60320 C13	≤16A/≤20A

<b>TOLERANCES</b> (UNLESS OTHERWISE SPECIFIED) LINEAR DIMENSIONS: .X = ± .500 .XX = ± .300 .XXX = ± .130 ANGULAR DIMENSIONS: X.X = ± 5° X.XX = ± .25° SYMBOLS (Q#) = CRITICAL DIM. (S) = COSMETIC SURFACE	UNLESS OTHERWISE SPECIFIED * INTERPRET DRAWING IAW ASME Y14.100-2000 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-1994 * REMOVE ALL BURRS AND SHARP EDGES 2 R MAX * DIMENSIONS ARE IN MILLIMETERS * TOLERANCES ARE: DECIMALS ±3 ANGLES ±1.0° DO NOT SCALE DRAWING	THIRD ANGLE PROJECTION 		SERVER TECHNOLOGY, INC. 1040 Sandhill Drive Reno, NV 89521
		APPROVALS DRAWN BY: MAR/	DATE 08/04/2010	
FINISH: VENDOR PART NO:	APPROVED BY: RELEASED BY:	SIZE D	CAGE CODE 04V90	DWG NO. 495-0370-4
		SCALE: 1/1	FILE NO: 495-0370-4.dwg	REV 1