

SERVER TECHNOLOGY, INC.
PROPRIETARY INFORMATION




THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

REV		DESCRIPTION	DATE	DFT/APPR
1		INITIAL DESIGN	08/04/2010	MAR/

NOTES:



ISO VIEW

Part Number	Input	Output
Model	Rating, North America / PSE Japan	Input Type
CB-24V1-C20	100-120V, 50/60Hz; 16A / 20A	IEC 60320 C20 Inlet
	Output Rating North America / PSE Japan	Outlet / PSE Japan
	100-120V, 50/60Hz; ≤16 A / ≤20 A	16 A (≤20 A)
	Outlet Type	Branch Circuit / PSE Japan
	NEMA 5-20R	≤16 A / ≤20 A

TOLERANCES (UNLESS OTHERWISE SPECIFIED) LINEAR DIMENSIONS: .X = ± .500 .XX = ± .300 .XXX = ± .130 ANGULAR DIMENSIONS: X.X = ± 5° X.XX = ± .25° SYMBOLS (Q#) = CRITICAL DIM. (S) = COSMETIC SURFACE	UNLESS OTHERWISE SPECIFIED * INTERPRET DRAWING IAW ASME Y14.100-2000 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-1994 * REMOVE ALL BURRS AND SHARP EDGES 2 R MAX * DIMENSIONS ARE IN MILLIMETERS * TOLERANCES ARE: DECIMALS ±3 ANGLES ±1.0° DO NOT SCALE DRAWING	THIRD ANGLE PROJECTION 		SERVER TECHNOLOGY, INC. 1040 Sandhill Drive Reno, NV 89521 DRAWING TITLE: BASIC CDU MODEL #CB-24V1-C20 16/20A, 120V BASIC WIRING DIAGRAM	
		APPROVALS DRAWN BY: MAR/ CHECKED BY: APPROVED BY: RELEASED BY:	DATE 08/04/2010		SIZE D
MATERIAL: FINISH: VENDOR PART NO:		SCALE: 1/1		FILE NO: 495-0371-1.dwg	SHEET 1 OF 1