

8

7

6

5

4

3

2

1

SERVER TECHNOLOGY, INC
PROPRIETARY INFORMATION

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.



THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

REVISION HISTORY				
ZONE	REV	DESCRIPTION	DATE	APPROVED
-	1	INITIAL DESIGN	1/13/2011	MB/

NOTES:

- 1. DIMENSIONS ARE IN MILLIMETERS AND [] ARE IN INCHES.
- 2. DIMENSIONS ARE NOMINAL. INFORMATION SUBJECT TO CHANGE WITHOUT NOTICE
- 3. MOUNTING BRACKETS CAN BE MOUNTED IN SEVERAL POSITIONS, SEE FIG. A, B, C, AND D.
- 4. MAXIMUM PANEL THICKNESS FOR BUTTON INTO KEYHOLE PANEL IS 2.3mm
- 5. HIDDEN BRACKETS SHOWN ARE DIFFERENT OPTIONS FOR MOUNTING.



DETAIL A
SCALE 1 / 5
CXG-24Vxxx-xxx (EXPANSION)

TOLERANCES (UNLESS OTHERWISE SPECIFIED) LINEAR DIMENSIONS: .X = ± .500 .XX = ± .300 .XXX = ± .150 ANGULAR DIMENSIONS: X = ± 1° X.X = ± .5° X.XX = ± .25° SYMBOLS (Q#) = CRITICAL DIM. (S) = COSMETIC SURFACE	UNLESS OTHERWISE SPECIFIED * INTERPRET DRAWING IAW ASME Y14.100-2000 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2007 * REMOVE ALL BURRS AND SHARP EDGES 2/R MAX. * DIMENSIONS ARE IN MILLIMETERS * DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING. DO NOT SCALE DRAWING	THIRD ANGLE PROJECTION 		SERVER TECHNOLOGY, INC. 1040 Sandhill Drive Reno, NV 89521	
		MATERIAL: FINISH: VENDOR PART NO:	APPROVALS DRAWN BY: MB CHECKED BY: MB/PG APPROVED BY: PG RELEASED BY:	DATE 1/13/2011 1/13/2011 1/13/2011	DRAWING TITLE: OUTLINE DRAWING, ENA-412-0375-42G
		SIZE B	CAGE CODE 04V90	DWG NO. 412-0375-42	REV 1
		SCALE: NONE	FILE NO: 412-0375-42.idw	SHEET 1	OF 1

8

7

6

5

4

3

2

1