

SERVER TECHNOLOGY, INC  
 PROPRIETARY INFORMATION




THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

| REVISIONS |                |            |          |
|-----------|----------------|------------|----------|
| REV       | DESCRIPTION    | DATE       | DFT/APPR |
| 1         | INITIAL DESIGN | 08/04/2010 | MAR/     |

NOTES:



ISO VIEW

| Part Number | Input                  |                    |                        | Output              |                             |                      |                          |                                  |               |  |
|-------------|------------------------|--------------------|------------------------|---------------------|-----------------------------|----------------------|--------------------------|----------------------------------|---------------|--|
|             | Rating, North America  | GS                 | PSE Japan              | Input Type          | Output Rating North America | GS                   | PSE Japan                | Outlet: North America / GS / PSE | Outlet Type   | Branch Circuit: North America / GS / PSE |
| CB-24V2-C20 | 208-240V, 50/60Hz; 16A | 230V, 50/60Hz; 16A | 200-240V, 50/60Hz; 20A | IEC 60320 C20 Inlet | 208-240V, 50/60Hz; ≤ 16A    | 230V, 50/60Hz; ≤ 16A | 200-240V, 50/60Hz; ≤ 20A | ≤ 12A / ≤ 10A / ≤ 15A            | IEC 60320 C13 | ≤ 16A / ≤ 16A / ≤ 20A                    |

|   |   |                            |              |  |              |
|---|---|----------------------------|--------------|--|--------------|
| <b>TOLERANCES</b><br>(UNLESS OTHERWISE SPECIFIED)<br>LINEAR DIMENSIONS:<br>.X = ± .500<br>.XX = ± .300<br>.XXX = ± .130<br>ANGULAR DIMENSIONS:<br>.XX = ± .5°<br>.XXX = ± .25°<br>SYMBOLS<br>(Q#) = CRITICAL DIM.<br>(S) = COSMETIC SURFACE | UNLESS OTHERWISE SPECIFIED<br>* INTERPRET DRAWING IAW ASME Y14.100-2000<br>* DIMENSIONING & TOLERANCING IAW ASME Y14.5M-1994<br>* REMOVE ALL BURRS AND SHARP EDGES .2 R MAX<br>* DIMENSIONS ARE IN MILLIMETERS<br>* TOLERANCES ARE: DECIMALS ±.3 ANGLES ±1.0°<br>DO NOT SCALE DRAWING | THIRD ANGLE PROJECTION<br> |              | SERVER TECHNOLOGY, INC.<br>1040 Sandhill Drive Reno, NV 89521<br>DRAWING TITLE:<br><b>BASIC CDU MODEL #CB-24V2-C20</b><br><b>16/20A, 208/240V BASIC</b><br><b>WIRING DIAGRAM</b><br>SIZE: D CAGE CODE: 04V90 DWG NO.: 495-0371-3 REV: 1<br>SCALE: 1/1 FILE NO: 495-0371-3.dwg SHEET 1 OF 1 |              |
|   | MATERIAL:   | APPROVALS                  | DATE         |  |              |
|   | FINISH:   | DRAWN BY:<br>MRAMSEY       | 08/04/2010   |  |              |
|   | VENDOR PART NO:   | CHECKED BY:                | APPROVED BY: |  | RELEASED BY: |