

SERVER TECHNOLOGY, INC
 PROPRIETARY INFORMATION




THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

REVISIONS			
REV	DESCRIPTION	DATE	DFT/APPR
1	INITIAL DESIGN	08/04/2010	MAR/

NOTES:



ISO VIEW

Part Number	Input			Output								
	Model	Rating, North America	GS	PSE Japan	Rating	Input Type	Output Rating North America	GS	PSE Japan	Outlet: North America / GS / PSE	Outlet Type	Branch Circuit: North America / GS / PSE
CB-12H2-C20		208-240V, 50/60Hz; 16A	230V, 50/60Hz; 16A	200-240V, 50/60Hz; 20A	IEC 60320 C20 Inlet		208-240V, 50/60Hz; ≤16A	230V, 50/60Hz; ≤16A	200-240V, 50/60Hz; ≤20A	≤12A/≤10A/≤15A	IEC 60320 C13	≤16A/≤16A/≤20A

TOLERANCES (UNLESS OTHERWISE SPECIFIED) LINEAR DIMENSIONS: .X = ±.500 .XX = ±.300 .XXX = ±.130 ANGULAR DIMENSIONS: .XX = ±.5° .XXX = ±.25° SYMBOLS (Q#) = CRITICAL DIM. (S) = COSMETIC SURFACE	UNLESS OTHERWISE SPECIFIED * INTERPRET DRAWING IAW ASME Y14.100-2000 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-1994 * REMOVE ALL BURRS AND SHARP EDGES .2 R MAX * DIMENSIONS ARE IN MILLIMETERS * TOLERANCES ARE: DECIMALS ±.3 ANGLES ±1.0° DO NOT SCALE DRAWING	THIRD ANGLE PROJECTION		SERVER TECHNOLOGY, INC. 1040 Sandhill Drive Reno, NV 89521 DRAWING TITLE: BASIC CDU MODEL #CB-12H2-C20 16/20A, 208/240V BASIC WIRING DIAGRAM SIZE CAGE CODE DWG NO. REV D 04V90 495-0370-3 1 SCALE: 1/1 FILE NO: 404-0370-3.dwg SHEET 1 OF 1
		APPROVALS	DATE	
		DRAWN BY: MRAMSEY	08/04/2010	
		CHECKED BY:		
MATERIAL:		APPROVED BY:		
FINISH:		RELEASED BY:		
VENDOR PART NO:				