



8 7 6 5 4 3 2 1

SERVER TECHNOLOGY, INC.  
 PROPRIETARY INFORMATION  
 THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.  
 THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

- NOTES:
1. DIMENSIONS ARE IN MILLIMETERS AND [ ] ARE IN INCHES.
  2. DIMENSIONS ARE NOMINAL. INFORMATION SUBJECT TO CHANGE WITHOUT NOTICE.
  3. MOUNTING BRACKETS CAN BE MOUNTED IN SEVERAL DIFFERENT POSITIONS, SEE FIG. A, B, C AND D.
  4. MAXIMUM PANEL THICKNESS FOR BUTTON INTO KEYHOLE PANEL IS 2.3mm.
  5. HIDDEN BRACKETS SHOWN ARE DIFFERENT OPTIONS FOR MOUNTING.



<b>TOLERANCES</b> (UNLESS OTHERWISE SPECIFIED) LINEAR DIMENSIONS: .X ± .500 .XX ± .300 .XXX ± .150 ANGULAR DIMENSIONS: X ± 1° X.X ± .5° X.XX ± .25°	UNLESS OTHERWISE SPECIFIED * INTERPRET DRAWING IAW ASME Y14.100-2010 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2007 * REMOVE ALL BURRS AND SHARP EDGES 2 R MAX. * DIMENSIONS ARE IN MILLIMETERS * DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING.	<b>SERVER TECHNOLOGY, INC.</b> 1040 Sandhill Drive Reno, NV 89521 DRAWING TITLE: <b>OUTLINE DRAWING, SWITCHED PIPS, V24</b>
	DO NOT SCALE DRAWING THIRD ANGLE PROJECTION 	
<b>SYMBOLS</b> (⊘) = CRITICAL DIM. (S) = COSMETIC SURFACE	<b>MATERIAL:</b>  <b>FINISH:</b>	SIZE: <b>B</b> CAGE CODE: <b>049V0</b> DWG NO.: <b>412-0375-52</b> SCALE: <b>NONE</b>
		REV: <b>1</b> SHEET: <b>3 OF 3</b>

8 7 6 5 4 3 2 1