

SERVER TECHNOLOGY, INC.
PROPRIETARY INFORMATION




RoHS COMPLIANT

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.


THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	DFT/APPR
1	INITIAL DESIGN	08/15/11	MB/PG

NOTES:



DETAIL A
 SCALE 1/3
 EXPANSION UNIT



Part Number	Expansion	Input	Output
Master	Expansion	Rating, North America	Input Type
CS-4HDX452B6	CL-4HDX452B6	240V 3W+PE, 50/60Hz; 48A	IEC 60309
CS-4HDV452B6	CL-4HDV452B6	240V 3W+PE, 50/60Hz; 40A	C58365C
CS-4HYY452B6	CL-4HYY452B6	120/208V 3W+N+PE, 50/60Hz; 48A	IEC 60309
Output Rating North America	Outlet: North America	Outlet Type	Branch Circuit: North America
240V, 50/60Hz; <= 83.1A	4x NEMA L15-30P <= 24A each	NEMA L15-30P	XYZ <= 30A
240V, 50/60Hz; <= 69.3A	4x NEMA L15-30P <= 24A each	NEMA L15-30P	XYZ <= 30A
208V, 50/60Hz; <= 83.1A	4x NEMA L15-30P <= 24A each	NEMA L15-30P	XYZ <= 30A

VHUYHUNHFKQR CR J \ # Q F

1040 Sandhill Drive Reno, NV 89521

DRAWING TITLE:
**FUNCTIONAL BLOCK WIRING DIAGRAM,
 SMART, H6**

SIZE B	CAGE CODE 049V0	DWG NO. 495-0476-2	REV 1
SCALE: 1/1	SHEET 1 OF 1		