


SERVER TECHNOLOGY, INC
 PROPRIETARY INFORMATION

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

REVISION HISTORY				
ZONE	REV	DESCRIPTION	DATE	APPROVED
-	1	INITIAL DESIGN	1/25/11	MB/VB



ISO VIEW

Part Number	Input		Input Type	Output		Outlet: North America	GS	Outlet Type
	Rating, North America	GS		Output Rating North America	GS			
C-48V4J454		230/400V 3W+N+PE, 50/60Hz; 16A	IEC 60309 16A		230V, 50/60Hz; <= 48A			48x C13 <= 10A each IEC 60320 C13
C-48V4K454		230/400V 3W+N+PE, 50/60Hz; 32A	IEC 60309 32A		230V, 50/60Hz; <= 96A			48x C13 <= 10A each IEC 60320 C13
C-48V52454	240/416V 3W+N+PE, 50/60Hz; 16A		NEMA L22-20P	240V, 50/60Hz; <= 48A		48x C13 <= 12A each		IEC 60320 C13
C-48V53454	240/416V 3W+N+PE, 50/60Hz; 16A		IEC 60309 16A	240V, 50/60Hz; <= 48A		48x C13 <= 12A each		IEC 60320 C13
C-48V54454	240/416V 3W+N+PE, 50/60Hz; 24A		IEC 60309 24A	240V, 50/60Hz; <= 72A		48x C13 <= 12A each		IEC 60320 C13
C-48V52454	240/416V 3W+N+PE, 50/60Hz; 24A		NEMA L22-30P	240V, 50/60Hz; <= 72A		48x C13 <= 12A each		IEC 60320 C13

TOLERANCES
 (UNLESS OTHERWISE SPECIFIED)
 CAB LENGTH (mm):
 0 - 50 = -0, +5
 51 - 200 = -0, +10
 201 - 500 = -0, +15
 501 - 1000 = -0, +20
 1001 - 2000 = -0, +25
 2001 - 4000 = -0, +30
 4001 AND GREATER = -0, +40

SHRINK TUBE AND INSULATION LENGTH (mm):
 X ± 10%

SYMBOLS
 (Q#) = CRITICAL DIM.
 (S) = COSMETIC SURFACE

UNLESS OTHERWISE SPECIFIED
 * INTERPRET DRAWING IAW ASME Y14.100-2000
 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2007
 * REMOVE ALL BURRS AND SHARP EDGES, 2/R MAX.
 * DIMENSIONS ARE IN MILLIMETERS
 * DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING.
 DO NOT SCALE DRAWING

MATERIAL:

FINISH:

VENDOR PART NO.:

THIRD ANGLE PROJECTION

APPROVALS	DATE
DRAWN BY: MB	1/24/2011
CHECKED BY: MB/VB	1/25/2011
APPROVED BY: VB	1/25/2011
RELEASED BY:	

SERVER TECHNOLOGY, INC.

1040 Sandhill Drive Reno, NV 89521

DRAWING TITLE:
 METERED CDU MODEL #C48V, 400V
 WIRING DIAGRAM

SIZE B	CAGE CODE 04V90	DWG NO. 495-0553-1	REV 1
SCALE NONE	FILE NO. 495-0553-1.dwg	SHEET 1	OF 1