



SERVER TECHNOLOGY, INC.
PROPRIETARY INFORMATION
 THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.
 THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

NOTES:

REVISIONS			
REV	DESCRIPTION	DATE	DFT/APPR
1	INITIAL DESIGN	6/15/11	MB/PG

Part Number	Expansion	Input	Output
Master	Expansion	Rating, North America	Input Type
CS-15HDX454C3-013	CL-15HDX454C3-013	240V 3W+PE, 50/60Hz; 48A	IEC 60309
CS-15HDV454C3-013	CL-15HDV454C3-013	240V 3W+PE, 50/60Hz; 40A	CS8365C
CS-15HY454C3-013	CL-15HY454C3-013	120/208V 3W+N+PE, 50/60Hz; 48A	IEC 60309

Output Rating North America	Outlet: North America	Outlet Type	Branch Circuit: North America	Phase: North America
240V, 50/60Hz; <=83.1A	12xC19 <= 16A each, 3xC13 <= 12A each	IEC 60320 C13 and C19	XY1, XY2, YZ1, YZ2 ,ZX1, ZX2 <= 20A	XY, YZ, ZX <= 27.7A
240V, 50/60Hz; <= 69.3A	12xC19 <= 16A each, 3xC13 <= 12A each	IEC 60320 C13 and C19	XY1, XY2, YZ1, YZ2 ,ZX1, ZX2 <= 20A	XY, YZ, ZX <= 23.1A
208V, 50/60Hz; <= 83.1A	12xC19 <= 16A each, 3xC13 <= 12A each	IEC 60320 C13 and C19	XY1, XY2, YZ1, YZ2 ,ZX1, ZX2 <= 20A	XY, YZ, ZX <= 27.7A

TOLERANCES (UNLESS OTHERWISE SPECIFIED)
 LINEAR DIMENSIONS:
 .X = ± .500
 .XX = ± .300
 .XXX = ± .150

ANGULAR DIMENSIONS:
 .X.X = ± 5°
 .X.XX = ± 25°

SYMBOLS
 (CRITICAL DIM.)
 (COSMETIC SURFACE)

UNLESS OTHERWISE SPECIFIED
 INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.100-2000
 DIMENSIONING & TOLERANCING IN ACCORDANCE WITH ASME Y14.5M-1994
 REMOVE ALL BURRS AND SHARP EDGES 2 R MAX
 DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING
 DO NOT SCALE DRAWING

THIRD ANGLE PROJECTION

MATERIAL:

FINISH:

VHUYHUN#HFKQR CR J / #DF
 1040 Sandhill Drive Reno, NV 89521

DRAWING TITLE:
FUNCTIONAL WIRING DIAGRAM
SMART, PIPS H15

SIZE: B
CAGE CODE: 04V90
DWG NO.:
SCALE: 1/1

REV 1
SHEET 1 OF 1