

8

7

6

5

4

3

2

1

SERVER TECHNOLOGY, INC
PROPRIETARY INFORMATION

RoHS COMPLIANT





THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

REVISION HISTORY				
ZONE	REV	DESCRIPTION	DATE	APPROVED
-	1	INITIAL DESIGN	1/20/2011	MB/

NOTES:

- 1. DIMENSIONS ARE IN MILLIMETERS AND [] ARE IN INCHES.
- 2. DIMENSIONS ARE NOMINAL. INFORMATION SUBJECT TO CHANGE WITHOUT NOTICE
- 3. MOUNTING BRACKETS CAN BE MOUNTED IN SEVERAL POSITIONS, SEE FIG. A, B, C, AND D.
- 4. MAXIMUM PANEL THICKNESS FOR BUTTON INTO KEYHOLE PANEL IS 2.3mm
- 5. HIDDEN BRACKETS SHOWN ARE DIFFERENT OPTIONS FOR MOUNTING.



TOLERANCES (UNLESS OTHERWISE SPECIFIED) LINEAR DIMENSIONS: .X = ± .500 .XX = ± .300 .XXX = ± .150 ANGULAR DIMENSIONS: X = ± 1° X.X = ± .5° X.XX = ± .25° SYMBOLS (Q#) = CRITICAL DIM. (S) = COSMETIC SURFACE	UNLESS OTHERWISE SPECIFIED * INTERPRET DRAWING IAW ASME Y14.100-2000 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2007 * REMOVE ALL BURRS AND SHARP EDGES, 2/R MAX. * DIMENSIONS ARE IN MILLIMETERS * DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING. DO NOT SCALE DRAWING	THIRD ANGLE PROJECTION 	SERVER TECHNOLOGY, INC. 1040 Sandhill Drive Reno, NV 89521	
			DRAWING TITLE: OUTLINE DWG. METERED V48 C13 400V 3PH WYE 6BR 32A TOP/FRONT ENTRY, MID DISP, BREAKERS, LN MONITORING	
MATERIAL: FINISH: VENDOR PART NO:		APPROVALS DRAWN BY: MB CHECKED BY: VB APPROVED BY: VB RELEASED BY:	DATE 1/20/2011 2/21/2011 2/21/2011	REV 1
SIZE: B CAGE CODE: 04V90 SCALE: NONE		DWG NO.: 412-0553-1 FILE NO.: 412-0553-1.dwg		SHEET 1 OF 3

8

7

6

5

4

3

2

1