


SERVER TECHNOLOGY, INC
 PROPRIETARY INFORMATION

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

| REVISION HISTORY | | | | |
|------------------|-----|----------------|---------|----------|
| ZONE | REV | DESCRIPTION | DATE | APPROVED |
| - | 1 | INITIAL DESIGN | 1/25/11 | MB/VB |



| Part Number | Input | | Output | | | | | |
|-------------|--------------------------------|--------------------------------|---------------|-----------------------------|----|-----------------------|----|---------------|
| | Rating, North America | GS | Input Type | Output Rating North America | GS | Outlet: North America | GS | Outlet Type |
| C-48V4I454 | | 230/400V 3W+N+PE, 50/60Hz; 16A | IEC 60309 16A | 230V, 50/60Hz <= 48A | | 48x C13 <= 10A each | | IEC 60320 C13 |
| C-48V4K454 | | 230/400V 3W+N+PE, 50/60Hz; 32A | IEC 60309 32A | 230V, 50/60Hz <= 96A | | 48x C13 <= 10A each | | IEC 60320 C13 |
| C-48V52454 | 240/416V 3W+N+PE, 50/60Hz; 16A | | NEMA L22-20P | 240V, 50/60Hz <= 48A | | 48x C13 <= 12A each | | IEC 60320 C13 |
| C-48V53454 | 240/416V 3W+N+PE, 50/60Hz; 16A | | IEC 60309 16A | 240V, 50/60Hz <= 48A | | 48x C13 <= 12A each | | IEC 60320 C13 |
| C-48V54454 | 240/416V 3W+N+PE, 50/60Hz; 24A | | IEC 60309 24A | 240V, 50/60Hz <= 72A | | 48x C13 <= 12A each | | IEC 60320 C13 |
| C-48V5Z454 | 240/416V 3W+N+PE, 50/60Hz; 24A | | NEMA L22-30P | 240V, 50/60Hz <= 72A | | 48x C13 <= 12A each | | IEC 60320 C13 |

ISO VIEW

TOLERANCES (UNLESS OTHERWISE SPECIFIED)
 CAB LENGTH (mm):
 0 - 50 = -0, +5
 51 - 200 = -0, +10
 201 - 500 = -0, +15
 501 - 1000 = -0, +20
 1001 - 2000 = -0, +30
 2001 - 4000 = -0, +35
 4001 AND GREATER = -0, +50

SHRINK TUBE AND INSULATION LENGTH (mm):
 X ± 10%

SYMBOLS
 (Q#) = CRITICAL DIM.
 (S) = COSMETIC SURFACE

UNLESS OTHERWISE SPECIFIED
 * INTERPRET DRAWING IAW ASME Y14.100-2000
 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2007
 * REMOVE ALL BURRS AND SHARP EDGES, 2/R MAX.
 * DIMENSIONS ARE IN MILLIMETERS
 * DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING.
 DO NOT SCALE DRAWING

MATERIAL:
 FINISH:
 VENDOR PART NO:

THIRD ANGLE PROJECTION

| APPROVALS | DATE |
|----------------------|-----------|
| DRAWN BY: MB | 1/24/2011 |
| CHECKED BY: MB/VB | 1/25/2011 |
| APPROVED BY: VB | 1/25/2011 |
| RELEASED BY: | |

SERVER TECHNOLOGY, INC.

1040 Sandhill Drive Reno, NV 89521

DRAWING TITLE:
METERED CDU MODEL #C48V, 400V WIRING DIAGRAM

| | | | |
|---------------|----------------------------|-----------------------|----------|
| SIZE B | CAGE CODE 04V90 | DWG NO. 495-0553-1 | REV 1 |
| SCALE NONE | FILE NO. 495-0553-1.dwg | SHEET 1 | OF 1 |