

SERVER TECHNOLOGY, INC.
PROPRIETARY INFORMATION



THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.


RoHS COMPLIANT

REVISIONS			
REV	DESCRIPTION	DATE	DFT/APPR
1	INITIAL DESIGN	08/04/2010	MAR/

NOTES:



ISO VIEW



Part Number	Input			Output			Outlet: North America / GS / PSE	Outlet Type	Branch Circuit: North America / GS / PSE
	Model	Rating, North America	GS	Rating, North America	GS	PSE Japan			
C-4H1-C20	100-120V, 50/60Hz; 16A			100-120V, 50/60Hz; 20A			100-120V, 50/60Hz; ≤20A	IEC 60320 C19	≤16A // ≤20A
C-4H1-L30	100-120V, 50/60Hz; 24A			100-120V, 50/60Hz; 30A			100-120V, 50/60Hz; ≤30A	IEC 60320 C19	≤16A // ≤20A
C-4H2-C20	208-240V, 50/60Hz; 16A			200-240V, 50/60Hz; 20A			200-240V, 50/60Hz; ≤20A	IEC 60320 C19	≤16A // ≤20A
C-4H2-L30	208-240V, 50/60Hz; 24A			200-240V, 50/60Hz; 30A			200-240V, 50/60Hz; ≤30A	IEC 60320 C19	≤16A // ≤20A
C-4HE-C20		230V, 50/60Hz; 16A					230V, 50/60Hz; ≤16A	IEC 60320 C19	/≤16A/
C-4HE-P32		230V, 50/60Hz; 32A					230V, 50/60Hz; ≤32A	IEC 60320 C19	/≤16A/

<p>TOLERANCES (UNLESS OTHERWISE SPECIFIED)</p> <p>LINEAR DIMENSIONS: .X = ±.500 .XX = ±.300 .XXX = ±.130</p> <p>ANGULAR DIMENSIONS: X.X = ± 5° X.XX = ± .25°</p> <p>SYMBOLS (Q#) = CRITICAL DIM. (S) = COSMETIC SURFACE</p>	<p>UNLESS OTHERWISE SPECIFIED</p> <p>* INTERPRET DRAWING IAW ASME Y14.100-2000</p> <p>* DIMENSIONING & TOLERANCING IAW ASME Y14.5M-1994</p> <p>* REMOVE ALL BURRS AND SHARP EDGES 2 R MAX</p> <p>* DIMENSIONS ARE IN MILLIMETERS</p> <p>* TOLERANCES ARE: DECIMALS ±3 ANGLES ±1.0°</p> <p>DO NOT SCALE DRAWING</p> <p>MATERIAL:</p> <p>FINISH:</p> <p>VENDOR PART NO:</p>	THIRD ANGLE PROJECTION		<p>SERVER TECHNOLOGY, INC.</p> <p>1040 Sandhill Drive Reno, NV 89521</p> <p>DRAWING TITLE: METERED CDU MODEL #C-4Hx-xxx 100/240V, 20/30A BASIC WIRING DIAGRAM</p> <p>SIZE: D CAGE CODE: 04V90 DWG NO.: 495-0368-1 REV: 1</p> <p>SCALE: 1/1 FILE NO: 495-0368-1.dwg SHEET: 1 OF 1</p>
		APPROVALS	DATE	
		DRAWN BY: MRAMSEY	08/04/2010	
		CHECKED BY:		
APPROVED BY:				
RELEASED BY:				