

SERVER TECHNOLOGY, INC.
PROPRIETARY INFORMATION



THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.


RoHS COMPLIANT

REV		DESCRIPTION	DATE	DFT/APPR
1		INITIAL DESIGN	08/04/2010	MAR/

NOTES:



Part Number	Input	Output
Model	Rating, North America	Rating, North America
C-24V2-C20M	208-240V, 50/60Hz, 16A	208-240V, 50/60Hz, 16A
C-24V2-L30M	208-240V, 50/60Hz, 24A	208-240V, 50/60Hz, 24A
C-24V2-C20M	230V, 50/60Hz, 16A	230V, 50/60Hz, 16A
C-24V2-L30M	230V, 50/60Hz, 24A	230V, 50/60Hz, 24A



ISO VIEW

TOLERANCES (UNLESS OTHERWISE SPECIFIED) LINEAR DIMENSIONS: .X = ± .500 .XX = ± .300 .XXX = ± .130 ANGULAR DIMENSIONS: X.X = ± 5° X.XX = ± .25°	UNLESS OTHERWISE SPECIFIED * INTERPRET DRAWING IAW ASME Y14.100-2000 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-1994 * REMOVE ALL BURRS AND SHARP EDGES 2 R MAX * DIMENSIONS ARE IN MILLIMETERS * TOLERANCES ARE: DECIMALS ±3 ANGLES ±1.0° DO NOT SCALE DRAWING	ISO VIEW 	SERVER TECHNOLOGY, INC. 1040 Sandhill Drive Reno, NV 89521	
			DRAWING TITLE: METERED CDU MODEL #C-24V2-C20M, L30M 208/240V BASIC WIRING DIAGRAM	
APPROVALS DRAWN BY: MRAMSEY CHECKED BY: APPROVED BY: RELEASED BY:	DATE 08/04/2010	SIZE: D SCALE: 1/1	CAGE CODE: 04V90 FILE NO: 495-0390-1.dwg	DWG NO.: 495-0390-1 SHEET: 1 OF 1