

SERVER TECHNOLOGY, INC.
PROPRIETARY INFORMATION




THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

REV		DESCRIPTION	DATE	DFT/APPR
1		INITIAL DESIGN	08/04/2010	MAR/

NOTES:



ISO VIEW

Part Number	Input	Output
Model	Rating, North America	Rating North America
C-16V2-C20MX	208-240V, 50/60Hz; 16A	208-240V, 50/60Hz; ≤16A
C-16VE-C20MX	230V, 50/60Hz; 16A	230V, 50/60Hz; ≤16A
CL-16V2-C20MX	208-240V, 50/60Hz; 16A	208-240V, 50/60Hz; ≤16A
CL-16VE-C20MX	230V, 50/60Hz; 16A	230V, 50/60Hz; ≤16A
CS-16V2-C20MX	208-240V, 50/60Hz; 16A	208-240V, 50/60Hz; ≤16A
CS-16VE-C20MX	230V, 50/60Hz; 16A	230V, 50/60Hz; ≤16A

<p>TOLERANCES (UNLESS OTHERWISE SPECIFIED)</p> <p>LINEAR DIMENSIONS: .X = ± .500 .XX = ± .300 .XXX = ± .130</p> <p>ANGULAR DIMENSIONS: X.X = ± 5° X.XX = ± .25°</p> <p>SYMBOLS (Q#) = CRITICAL DIM. (S) = COSMETIC SURFACE</p>	<p>UNLESS OTHERWISE SPECIFIED * INTERPRET DRAWING IAW ASME Y14.100-2000 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-1994 * REMOVE ALL BURRS AND SHARP EDGES 2 R MAX * DIMENSIONS ARE IN MILLIMETERS * TOLERANCES ARE: DECIMALS ±3 ANGLES ±1.0° DO NOT SCALE DRAWING</p> <p>MATERIAL:</p> <p>FINISH:</p> <p>VENDOR PART NO:</p>	<p>THIRD ANGLE PROJECTION</p>	<p>SERVER TECHNOLOGY, INC.</p> <p>1040 Sandhill Drive Reno, NV 89521</p>			
			<p>DRAWING TITLE: METERED CDU MODEL #C-16V2-C20MX 208V BASIC WIRING DIAGRAM</p>			
			<p>APPROVALS</p> <p>DRAWN BY: MRAMSEY</p> <p>CHECKED BY:</p> <p>APPROVED BY:</p> <p>RELEASED BY:</p>	<p>DATE</p> <p>08/04/2010</p>	<p>SIZE</p> <p>D</p>	<p>CAGE CODE</p> <p>04V90</p>
			<p>SCALE: 1/1</p>	<p>FILE NO: 495-0335-2.dwg</p>	<p>DWG NO. 495-0335-2</p>	<p>REV 1</p>