

8 7 6 5 4 3 2 1

SERVER TECHNOLOGY, INC  
 PROPRIETARY INFORMATION





RoHS COMPLIANT

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

REVISION HISTORY				
ZONE	REV	DESCRIPTION	DATE	APPROVED
-	1	INITIAL DESIGN	10/28/08	MAR/

NOTES:


1. DIMENSIONS ARE IN MILLIMETERS AND [ ] BRACKETS ARE IN INCHES.
2. DIMENSIONS ARE NOMINAL. INFORMATION SUBJECT TO CHANGE WITHOUT NOTICE.



**CL-36V4**  
(LINKED)  
**DETAIL A**

UNLESS OTHERWISE SPECIFIED  
 \* INTERPRET DRAWING IAW ASME Y14.100-2000  
 \* DIMENSIONING & TOLERANCING IAW ASME Y14.5M-1994  
 \* REMOVE ALL BURRS AND SHARP EDGES .2 R MAX  
 \* DIMENSIONS ARE IN MILLIMETERS  
 \* TOLERANCES ARE: DECIMALS ± .3 ANGLES ± 1.0°  
 DO NOT SCALE DRAWING

THIRD ANGLE PROJECTION



**SERVER TECHNOLOGY, INC.**  
 1040 Sandhill Drive Reno, NV 89521

MATERIAL:  
**SEE SEPARATE BOM**

FINISH:  
**SEE SEPARATE BOM**

VENDOR PART NO:

APPROVALS

DRAWN BY:  
**M. RAMSEY**

CHECKED BY:

APPROVED BY:

RELEASED BY:

DATE

10/28/08

DATE

DATE

DATE

DRAWING TITLE:  
**OUTLINE DRAWING, SMART CDU  
 CS-36V4-xx MODEL, WITH  
 MOUNTING BRACKET OPTIONS**

SIZE	CAGE CODE	DWG NO.	REV
B	04V90	412-0333-2	1

SCALE: NTS	FILE NO: 412-0333-2.idw	SHEET 1 OF 3
------------	-------------------------	--------------

8 7 6 5 4 3 2 1

SERVER TECHNOLOGY, INC  
 PROPRIETARY INFORMATION



RoHS COMPLIANT

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.


REVISION HISTORY				
ZONE	REV	DESCRIPTION	DATE	APPROVED
-	1	INITIAL DESIGN	10/28/08	MAR/

NOTES:


1. DIMENSIONS ARE IN MILLIMETERS ARE [ ] BRACKETS ARE IN INCHES.
2. MOUNTING BRACKETS CAN BE MOUNTED IN SEVERAL DIFFERENT POSITIONS SEE FIG. A, B, C, AND D.
3. SEE MOUNTING KIT (KIT-MBNF2-1) DRAWING #406-0070-7 FOR DETAILS.
4. MAXIMUM PANEL THICKNESS FOR BUTTON INTO KEYHOLE PANEL IS 2.3MM.
5. DIMENSIONS ARE NOMINAL. INFORMATION SUBJECT TO CHANGE WITHOUT NOTICE.




2 FIG. A  
 MB-0005-IPT7




2 FIG. B  
 MB-0005-IPT7



2 FIG. C  
 MB-0005-IPT7



2 FIG. D  
 MB-0005-IPT7



DETAIL A

UNLESS OTHERWISE SPECIFIED * INTERPRET DRAWING IAW ASME Y14.100-2000 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-1994 * REMOVE ALL BURRS AND SHARP EDGES. 2 R MAX * DIMENSIONS ARE IN MILLIMETERS * TOLERANCES ARE: DECIMALS ± .3 ANGLES ± 1.0° DO NOT SCALE DRAWING		THIRD ANGLE PROJECTION 		<b>SERVER TECHNOLOGY, INC.</b> 1040 Sandhill Drive Reno, NV 89521	
MATERIAL: SEE SEPARATE BOM		APPROVALS M. RAMSEY		DATE 10/28/08	
FINISH: SEE SEPARATE BOM		CHECKED BY:		DRAWING TITLE: OUTLINE DRAWING, SMART CDU CS-36V4-xx MODEL, WITH MOUNTING BRACKET OPTIONS	
VENDOR PART NO:		APPROVED BY:		SIZE CAGE CODE DWG NO. REV B 04V90 412-0333-2 1	
		RELEASED BY:		SCALE: NTS FILE NO: 412-0333-2.idw SHEET 2 OF 3	

8

7

6

5

↓

4

3

2

1

SERVER TECHNOLOGY, INC  
PROPRIETARY INFORMATION

RoHS COMPLIANT

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

REVISION HISTORY				
ZONE	REV	DESCRIPTION	DATE	APPROVED
-	1	INITIAL DESIGN	10/28/08	MAR/

NOTES:

- 1. DIMENSIONS ARE IN MILLIMETERS AND [ ] BRACKETS ARE IN INCHES.
- 2. HIDDEN BRACKETS SHOWN ARE DIFFERENT OPTIONS FOR MOUNTING.
- 3. SEE MOUNTING BRACKET KIT (KIT-MBNF2-1) DRAWING #406-0070-7 FOR DETAILS.
- 4. DIMENSIONS ARE NOMINAL. INFORMATION SUBJECT TO CHANGE WITHOUT NOTICE.

D

D

C



C

B

B

A

A



<small>UNLESS OTHERWISE SPECIFIED</small> <small>* INTERPRET DRAWING IAW ASME Y14.100-2000</small> <small>* DIMENSIONING &amp; TOLERANCING IAW ASME Y14.5M-1994</small> <small>* REMOVE ALL BURRS AND SHARP EDGES .2 R MAX</small> <small>* DIMENSIONS ARE IN MILLIMETERS</small> <small>* TOLERANCES ARE: DECIMALS ± .3 ANGLES ± 1.0°</small> <small>DO NOT SCALE DRAWING</small>		<small>THIRD ANGLE PROJECTION</small> 		<b>SERVER TECHNOLOGY, INC.</b> <small>1040 Sandhill Drive Reno, NV 89521</small>	
<small>MATERIAL:</small> <b>SEE SEPARATE BOM</b>		<small>APPROVALS</small> <b>M. RAMSEY</b>		<small>DATE</small> <b>10/28/08</b>	
<small>FINISH:</small> <b>SEE SEPARATE BOM</b>		<small>CHECKED BY:</small>		<small>DRAWING TITLE:</small> <b>OUTLINE DRAWING, SMART CDU CS-36V4-xx MODEL, WITH MOUNTING BRACKET OPTIONS</b>	
<small>VENDOR PART NO:</small>		<small>APPROVED BY:</small>		<small>SIZE</small> <b>B</b> <small>CAGE CODE</small> <b>04V90</b> <small>DWG NO.</small> <b>412-0333-2</b> <small>REV</small> <b>1</b>	
		<small>RELEASED BY:</small>		<small>SCALE:</small> <b>NTS</b> <small>FILE NO:</small> <b>412-0333-2.idw</b> <small>SHEET</small> <b>3 OF 3</b>	

8

7

6

5

↑

4

3

2

1