

SERVER TECHNOLOGY, INC
 PROPRIETARY INFORMATION

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.



THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

REVISION HISTORY				
ZONE	REV	DESCRIPTION	DATE	APPROVED
	1	INITIAL DESIGN	6/20/2011	CC/VB

NOTES:

1. SEE STI QUALITY STANDARD #104-1000-01 FOR GENERAL REQUIREMENTS.



part number	Expansion	Input Rating, North America	CS	Input Type	Output Rating North America	CS	Outlet: North America	CS	Outlet Type	Branch Circuit: North America / GS	Phase: North America / GS	
CS-24VW425A9	CL-24VW425A9			230/400V 3W4NPF, 50/60Hz, 16A	IEC 60309 16A		230V, 50/60Hz, <=48A		12xC19 <=16A each, 12xC13 <=18A each	IEC 60320 C13 / C19	/11a, 11b, 12a, 12b, 13a, 13b <=16A	/11, 12, 13 <=16A
CS-24VW425A9/BA	CL-24VW425A9/BA			230/400V 3W4NPF, 50/60Hz, 32A	IEC 60309 32A		230V, 50/60Hz, <=96A		12xC19 <=16A each, 12xC13 <=18A each	IEC 60320 C13 / C19	/11a, 11b, 12a, 12b, 13a, 13b <=16A	/11, 12, 13 <=32A
CS-24VW425A9/BB	CL-24VW425A9/BB			230/400V 3W4NPF, 50/60Hz, 32A	IEC 60309 32A		230V, 50/60Hz, <=96A		12xC19 <=16A each, 12xC13 <=18A each	IEC 60320 C13 / C19	/11a, 11b, 12a, 12b, 13a, 13b <=16A	/11, 12, 13 <=32A
CS-24V52425A9	CL-24V52425A9	240/415V 3W4NPF, 50/60Hz, 16A		NEMA L22-20P	240V, 50/60Hz, <=48A		12xC19 <=16A each, 12xC13 <=12A each		IEC 60320 C13 / C19	/11a, 11b, 12a, 12b, 13a, 13b <=20A/	/11, 12, 13 <=16A/	
CS-24V53425A9	CL-24V53425A9	240/415V 3W4NPF, 50/60Hz, 16A		IEC 60309 16A	240V, 50/60Hz, <=48A		12xC19 <=16A each, 12xC13 <=12A each		IEC 60320 C13 / C19	/11a, 11b, 12a, 12b, 13a, 13b <=20A/	/11, 12, 13 <=16A/	
CS-24V54425A9	CL-24V54425A9	240/415V 3W4NPF, 50/60Hz, 24A		IEC 60309 24A	240V, 50/60Hz, <=72A		12xC19 <=16A each, 12xC13 <=12A each		IEC 60320 C13 / C19	/11a, 11b, 12a, 12b, 13a, 13b <=20A/	/11, 12, 13 <=24A/	
CS-24V52425A9	CL-24V52425A9	240/415V 3W4NPF, 50/60Hz, 24A		NEMA L22-30P	240V, 50/60Hz, <=72A		12xC19 <=16A each, 12xC13 <=12A each		IEC 60320 C13 / C19	/11a, 11b, 12a, 12b, 13a, 13b <=20A/	/11, 12, 13 <=24A/	

ISO VIEW

TOLERANCES (UNLESS OTHERWISE SPECIFIED):
 LINEAR DIMENSIONS:
 X = ± .500
 .XX = ± .200
 .XXX = ± .130

ANGULAR DIMENSIONS:
 X = ± 1°
 .XX = ± .5°
 .XXX = ± .25°

SYMBOLS
 (G#) = CRITICAL DIM.
 (S) = COSMETIC SURFACE

UNLESS OTHERWISE SPECIFIED
 * INTERPRET DRAWING IAW ASME Y14.100-2000
 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2007
 * REMOVE ALL BURRS AND SHARP EDGES 2 R MAX
 * DIMENSIONS ARE IN MILLIMETERS
 * DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING.

DO NOT SCALE DRAWING
 THIRD ANGLE PROJECTION

MATERIAL:
 FINISH:

SERVER TECHNOLOGY, INC.
 1040 Sandhill Drive Reno, NV 89521

DRAWING TITLE:
**FUNCTIONAL BLOCK WIRING DIAGRAM,
 SMART PIPS V24**

SIZE B CAGE CODE 049V0 DWG NO. 495-0615-1 REV 1

SCALE NONE SHEET 1 OF 1