




SERVER TECHNOLOGY, INC.
PROPRIETARY INFORMATION
 THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.
 THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.


RoHS COMPLIANT

NOTES:

REVISIONS			
REV	DESCRIPTION	DATE	DFT/APPR
1	INITIAL DESIGN	06/24/11	MB/PG



Part Number	Expansion	Input	Output					
Master	Expansion	Rating, North America	Input Type	Output Rating North America	Outlet: North America	Outlet Type	Branch Circuit: North America	Phase: North America
CS-6H52454B4	CL-6H52454B4	240/415V 3W+N+PE, 50/60Hz; 16A	NEMA L22-20P	240V, 50/60Hz; <= 48A	6xNEMA L6-30R <= 16A each	NEMA L6-30R	L1a, L1b, L2a, L2b, L3a, L3b <= 20A	L1, L2, L3 <= 16A
CS-6H53454B4	CL-6H53454B4	240/415V 3W+N+PE, 50/60Hz; 16A	IEC 60309 16A	240V, 50/60Hz; <= 48A	6xNEMA L6-30R <= 16A each	NEMA L6-30R	L1a, L1b, L2a, L2b, L3a, L3b <= 20A	L1, L2, L3 <= 16A
CS-6H54454B4	CL-6H54454B4	240/415V 3W+N+PE, 50/60Hz; 24A	IEC 60309 24A	240V, 50/60Hz; <= 72A	6xNEMA L6-30R <= 24A each	NEMA L6-30R	L1a, L1b, L2a, L2b, L3a, L3b <= 20A	L1, L2, L3 <= 24A
CS-6H5Z454B4	CL-6H5Z454B4	240/415V 3W+N+PE, 50/60Hz; 24A	NEMA L22-30P	240V, 50/60Hz; <= 72A	6xNEMA L6-30R <= 24A each	NEMA L6-30R	L1a, L1b, L2a, L2b, L3a, L3b <= 20A	L1, L2, L3 <= 24A



DETAIL A
 SCALE 1/3
 EXPANSION UNIT

TOLERANCES (UNLESS OTHERWISE SPECIFIED) LINEAR DIMENSIONS: .X = ± .500 .XX = ± .300 .XXX = ± .150 ANGULAR DIMENSIONS: .X.X = ± 5° .X.XX = ± 25°	UNLESS OTHERWISE SPECIFIED • INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.100-2000 • DIMENSIONS & TOLERANCES IN MILLIMETERS UNLESS OTHERWISE SPECIFIED • REMOVE ALL BURRS AND SHARP EDGES: 2 R MAX • DIMENSIONS ARE IN MILLIMETERS • DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING DO NOT SCALE DRAWING	VHUYHUNFKQR CR J #DF 1040 Sandhill Drive Reno, NV 89521 DRAWING TITLE: FUNCTIONAL WIRING DIAGRAM CS[CL]-6H5
	THIRD ANGLE PROJECTION 	
SYMBOLS (⊕) = CRITICAL DIM. (⊙) = COSMETIC SURFACE	MATERIAL: FINISH:	SIZE: B CAGE CODE: 04V90 DWG NO.: 495-0476-4 SCALE: 1/1 REV: 1 SHEET: 1 OF 1