



SERVER TECHNOLOGY, INC.
PROPRIETARY INFORMATION
 THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.
 THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

REV		DESCRIPTION	DATE	DFT/APPR
1		INITIAL DESIGN	06/30/11	MB/TI

NOTES:



Part Number	Expansion	Input	Output					
Master	Expansion	Rating, North America	Input Type	Output Rating North America	Outlet: North America	Outlet Type	Branch Circuit: North America	Phase: North America
CS-36VDD458A4	CL-36VDD458A4	240V 3W+PE, 50/60Hz; 16A	NEMA L15-20P	240V, 50/60Hz; <= 27.7A	12xC19 <=9.2A each, 24xC13 <= 9.2A each	IEC 60320 C13 / C19	XY, YZ, ZX <= 9.2A	XY, YZ, ZX <= 9.2A
CS-36VDE458A4	CL-36VDE458A4	240V 3W+PE, 50/60Hz; 24A	NEMA L15-30P	240V, 50/60Hz; <= 41.6A	12xC19 <= 13.9A each, 24xC13 <= 12A each	IEC 60320 C13 / C19	XY, YZ, ZX <= 13.9A	XY, YZ, ZX <= 13.9A
CS-36VYL458A4	CL-36VYL458A4	120/208V 3W+N+PE, 50/60Hz; 16A	NEMA L21-20P	208V, 50/60Hz; <= 27.7A	12xC19 <=9.2A each, 24xC13 <= 9.2A each	IEC 60320 C13 / C19	XY, YZ, ZX <= 9.2A	XY, YZ, ZX <= 9.2A
CS-36VYM458A4	CL-36VYM458A4	120/208V 3W+N+PE, 50/60Hz; 24A	NEMA L21-30P	208V, 50/60Hz; <= 41.6A	12xC19 <= 13.9A each, 24xC13 <= 12A each	IEC 60320 C13 / C19	XY, YZ, ZX <= 13.9A	XY, YZ, ZX <= 13.9A

TOLERANCES (UNLESS OTHERWISE SPECIFIED) LINEAR DIMENSIONS: .X = ± .500 .XX = ± .300 .XXX = ± .150 ANGULAR DIMENSIONS: .X.X = ± 5° .X.XX = ± .25° SYMBOLS (Q) = CRITICAL DIM. (S) = COSMETIC SURFACE	UNLESS OTHERWISE SPECIFIED INTERPRET DRAWING IN ACCORDANCE WITH ASME Y14.100-2000 DIMENSIONING & TOLERANCING IN ACCORDANCE WITH ASME Y14.5M-1994 REMOVE ALL BURRS AND SHARP EDGES 2 R MAX DIMENSIONS ARE IN MILLIMETERS DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING DO NOT SCALE DRAWING	VHUYHUN#HFQQR CR J \#DF 1040 Sandhill Drive Reno, NV 89521 DRAWING TITLE: WIRING DIAGRAM, BASIC, CS[CL]-36VD
	THIRD ANGLE PROJECTION 	
MATERIAL: FINISH:	SCALE: 1/1	CAGE CODE: 04V90 DWG NO.: 495-0475-3 REV: 1 SHEET: 1 OF 1