



SERVER TECHNOLOGY, INC  
 PROPRIETARY INFORMATION

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

- NOTES:
1. DIMENSIONS ARE IN MILLIMETERS AND [ ] ARE IN INCHES.
  2. DIMENSIONS ARE NOMINAL. INFORMATION SUBJECT TO CHANGE WITHOUT NOTICE.
- HIDDEN BRACKETS SHOWN ARE DIFFERENT OPTIONS FOR MOUNTING.
3. MAXIMUM PANEL THICKNESS FOR BUTTON INTO KEYHOLE PANEL IS 2.3mm



<b>TOLERANCES</b> <small>(UNLESS OTHERWISE SPECIFIED)</small> <b>LINEAR DIMENSIONS:</b> X = ± .500 .XX = ± .200 .XXX = ± .130  <b>ANGULAR DIMENSIONS:</b> X = ± 1° .XX = ± .5° .XXX = ± .25°	<b>UNLESS OTHERWISE SPECIFIED</b> * INTERPRET DRAWING IAW ASME Y14.100-2000 * DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2007 * REMOVE ALL BURRS AND SHARP EDGES 2 R MAX * DIMENSIONS ARE IN MILLIMETERS * DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING.
	<b>DO NOT SCALE DRAWING</b> <b>THIRD ANGLE PROJECTION</b> 
<b>SYMBOLS</b> (G#) = CRITICAL DIM. (S) = COSMETIC SURFACE	<b>MATERIAL:</b>  <b>FINISH:</b>

**SERVER TECHNOLOGY, INC.**

1040 Sandhill Drive Reno, NV 89521

**DRAWING TITLE:**  
 Outline DWG, Smart Pips V36 (24)C13  
 (12)C19 208V 3PH Delta, 3BR, 30A, Center  
 Display, Top/Top Front Entry

SIZE <b>B</b>	CAGE CODE <b>049V0</b>	DWG NO. <b>412-0475-3</b>	REV <b>1</b>
SCALE <b>NONE</b>	SHEET <b>3</b>		OF 3