




SERVER TECHNOLOGY, INC
 PROPRIETARY INFORMATION

THIS DOCUMENT IS THE SOLE PROPERTY OF SERVER TECHNOLOGY, INC. THE RELEASE OF DATA CONTAINED IN THIS DOCUMENT AND THE REPRODUCTION OF THIS DOCUMENT, IN WHOLE OR IN PART, WITHOUT THE WRITTEN PERMISSION OF SERVER TECHNOLOGY, INC IS PROHIBITED.

THESE COMMODITIES, TECHNOLOGY OR SOFTWARE WERE EXPORTED FROM THE UNITED STATES IN ACCORDANCE WITH THE EXPORT ADMINISTRATION REGULATIONS. DIVERSION CONTRARY TO U.S. LAW IS PROHIBITED.

RoHS COMPLIANT

REVISION HISTORY				
ZONE	REV	DESCRIPTION	DATE	APPROVED
-	1	INITIAL DESIGN	9/17/2010	MAR/
-	2	RELOCATED POWER DISTRIBUTION BOARD	9/17/2010	MAR/



Part Number	Expansion	Input	Output	Outlet: North America	GS	Outlet Type	Branch Circuit: North America / GS	Phase: North America / GS
Mister	Rating, North America	GS	Input Type	Output Rating, North America	GS	Outlet: North America	GS	
CS-24H4894A1	CL-24H4894A1	230/100V/3W/HP, 50/60Hz, 16A	IEC 60309 16A	230V, 50/60Hz, <=48A		6C19<-16Aeach, 18C13<-10Aeach	IEC60309C19 / 11a, 11b, 12a, 12b, 13a, 13b<-16A	/ 11, 12, 13<-16A
CS-24H524894A1	CL-24H524894A1	230/100V/3W/HP, 50/60Hz, 32A	IEC 60309 32A	230V, 50/60Hz, <=96A		6C19<-16Aeach, 18C13<-10Aeach	IEC60309C19 / 11a, 11b, 12a, 12b, 13a, 13b<-16A	/ 11, 12, 13<-32A
CS-24H524894A1	CL-24H524894A1	240/116V/3W/HP, 50/60Hz, 16A	NEMA12-20P	240V, 50/60Hz, <=48A		6C19<-16Aeach, 18C13<-12Aeach	IEC60309C19 / 11a, 11b, 12a, 12b, 13a, 13b<-20A	/ 11, 12, 13<-16A/
CS-24H524894A1	CL-24H524894A1	240/116V/3W/HP, 50/60Hz, 16A	IEC 60309 16A	240V, 50/60Hz, <=48A		6C19<-16Aeach, 18C13<-12Aeach	IEC60309C19 / 11a, 11b, 12a, 12b, 13a, 13b<-20A/	/ 11, 12, 13<-16A/
CS-24H54894A1	CL-24H54894A1	240/116V/3W/HP, 50/60Hz, 24A	IEC 60309 24A	240V, 50/60Hz, <=72A		6C19<-16Aeach, 18C13<-12Aeach	IEC60309C19 / 11a, 11b, 12a, 12b, 13a, 13b<-20A/	/ 11, 12, 13<-24A/
CS-24H524894A1	CL-24H524894A1	240/116V/3W/HP, 50/60Hz, 24A	NEMA12-30P	240V, 50/60Hz, <=72A		6C19<-16Aeach, 18C13<-12Aeach	IEC60309C19 / 11a, 11b, 12a, 12b, 13a, 13b<-20A/	/ 11, 12, 13<-24A/

TOLERANCES
 (UNLESS OTHERWISE SPECIFIED)
 LINEAR DIMENSIONS:
 .X = ± .500
 .XX = ± .300
 .XXX = ± .150

ANGULAR DIMENSIONS:
 X = ± 1°
 X.X = ± .5°
 X.XX = ± .25°

SYMBOLS
 (Q) = CRITICAL DIM.
 (S) = COSMETIC SURFACE

UNLESS OTHERWISE SPECIFIED
 • INTERPRET DRAWING IAW ASME Y14.100-2000
 • DIMENSIONING & TOLERANCING IAW ASME Y14.5M-2007
 • REMOVE ALL BURRS AND SHARP EDGES, 2/R MAX.
 • DIMENSIONS ARE IN MILLIMETERS
 • DIMENSIONAL LIMITS APPLY AFTER PLATING/COATING.
 DO NOT SCALE DRAWING

MATERIAL:
 SEE SEPARATE BOM

FINISH:
 SEE SEPARATE BOM

VENDOR PART NO:

THIRD ANGLE PROJECTION

APPROVALS	DATE
DRAWN BY: mramsey	9/17/2010
CHECKED BY: MAR/JM	10/5/2010
APPROVED BY: MAR/JM	10/5/2010
RELEASED BY: MAR/JM	10/5/2010

SERVER TECHNOLOGY, INC.
 1040 Sandhill Drive Reno, NV 89521

DRAWING TITLE:
**OUTLINE DRAWING, CDU CS-24H4/5,
 PIPS MODELS w/ MOUNTING BRACKET
 OPTIONS**

SIZE B	CAGE CODE 04V90	DWG NO. 495-0483-1	REV 2
SCALE: NONE	FILE NO: 495-0483-1.dwg	SHEET 1	OF 1