

# Sentry Smart CDU

## CS-18V

### High Density Power Distribution

The Smart Cabinet Distribution Units (CDU) provide reliable power distribution combined with local and remote power monitoring and environmental monitoring via IP. Use the network interface to view power, temperature and humidity levels via Web browser, or receive SNMP-based alarms and email alerts when conditions exceed defined thresholds.

The Smart CDU family has the capability to daisy chain units together. The Expansion CDU Module gives the ability to use one IP address across different power circuits.

### Additional Benefits:



#### Branch Circuit Protection

The Sentry CDU Family meets the new UL 60950-1 requirement for branch circuit protection.

- UL 489 rated circuit breakers



#### Input Current Monitoring

The NEW Digital True RMS current monitoring, with improved accuracy, is critical to preventing overloads in high-density computing environments. There are six LED digital displays on the CDU enclosure which report the input current of each branch circuit for simple load balancing.



#### Temperature and Humidity

The Smart CDU supports two external 10' (3m) probes. Each of these probes measure both temperature and humidity. Receive SNMP-based alerts or email notifications when conditions exceed defined thresholds.



#### Linking for Smart CDU (Expansion Modules)

The Smart CDU family has the capability to daisy chain units together. The Expansion Module provides the ability to link two power circuits under one IP address.

## Key Features

- > High Density: Single-power input feed; 18 outlets per enclosure (Qty 12 x IEC C19 and qty 6 x IEC C13 outlets)
- > High Power Distribution: Three phase 208-240V power options; 50 and 60 Amp power input feed
- > Input Current Monitor: Precisely measure the aggregate current draw (in amps) on each power circuit. On-site verification of the input current with the LED digital display. This units has six LEDs total; one for each of the six branches. Remote verification via web browser or serial screen.
- > IP Access & Security: Web interface, SSL, SSH, Telnet, SNMP, FTP, SNTp, Syslog, LDAP, LDAPS, RADIUS, TACACS and RS-232 access
- > SNMP Traps & Alerts: Provide automated SNMP-based alarms or Email alerts for power and environmental conditions
- > Environmental Monitoring: Each Smart CDU supports two external temperature & humidity probes and reports conditions thru the user interface without the need for additional IP addresses
- > Add an Expansion Module: Daisy chain the Smart CDU Expansion Module (CS/CL) for power monitoring of separate power circuits from a single IP address



Model	Available Input Voltages	Amperage	Available Input Cord**	Outlets	Dimensions (L x W x D)
CS-18VDX813A2 CL-18VDX813A2*	3-Phase Delta, 208 V 50/60Hz	60A	IEC 60309 60A Cordset, 10 ft (3m)	(12) IEC 60320/C19 (6) IEC 60320/C13	68.0 x 1.75 x 3.5 in. (1727 x 44.4 x 88.9 mm)
CS-18VYY813A2 CL-18VYY813A2*	3-Phase Wye, 208 V 50/60Hz	60A	IEC 60309 60A Cordset, 10 ft (3m)	(12) IEC 60320/C19 (6) IEC 60320/C13	68.0 x 1.75 x 3.5 in. (1727 x 44.4 x 88.9 mm)
CS-18VDV413A2 CL-18VDV413A2*	3-Phase Delta, 208 V 50/60Hz	50A	CS8365 Cordset, 10 ft (3m)	(12) IEC 60320/C19 (6) IEC 60320/C13	68.0 x 1.75 x 3.5 in. (1727 x 44.4 x 88.9 mm)

\* CL part numbers refer to the Expansion CDU

\*\* Bottom Cord entry for Input cord

## Additional Features and Specifications

### Agency Approvals

- > US & Canada (cULus mark) to UL 60950-1:2003 and CAN/CSA 22.2 No. 60950-1-03
- > FCC Class A, Part 15
- > CE
- > EMC to EN 55022 Class A, EN 55024
- > CISPR 22 Class A

### Communications and Security

- > 10/100 BaseT Ethernet
- > HTTP/HTTPS
- > SSLv3/TLSv1
- > SNMPv2
- > SSHv2
- > Telnet
- > LDAPS/LDAPv3
- > TACACS+
- > RADIUS
- > RS-232 (Serial)

### Branch Circuit Protection

- > Compliant to UL 60950-1

### Accessories

- > Optional Temperature & Humidity Probe
  - EMTH-1-1 Temperature & Humidity Probe, 10 ft (3m)



## Server Technology

HEADQUARTERS - NORTH AMERICA  
 Server Technology, Inc.  
 1040 Sandhill Drive  
 Reno, NV 89521  
 United States  
 1.775.284.2000 Tel  
 1.775.284.2065 Fax  
 sales@servertech.com  
 www.servertech.com  
 www.servertechblog.com

EMEA  
 Server Technology Intl  
 Sienna Court  
 The Broadway  
 Maidenhead  
 Berkshire  
 SL6 1NJ  
 United Kingdom  
 +44 (0) 1628 509053 Tel  
 +44 (0) 1628 509100 Fax  
 salesintl@servertech.com

APAC  
 Server Technology Intl  
 37th Floor, Singapore Land  
 Tower  
 50 Raffles Place  
 Singapore 048623  
 +65 (0) 6829 7008 Tel  
 +65 (0) 6234 4574 Fax  
 salesintl@servertech.com